



## Mre11 Antibody [12D7]

CATALOG NUMBER: 47-148

### Specifications

<b>SPECIES REACTIVITY:</b>	Human
<b>TESTED APPLICATIONS:</b>	IHC, WB
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>IMMUNOGEN:</b>	GST fusion protein corresponding to aa 182-582 of Mre11 expressed in E. coli.
<b>HOST SPECIES:</b>	Mouse

### Properties

<b>PURIFICATION:</b>	Protein G-purified
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	PBS containing 0.01% sodium azide.
<b>STORAGE CONDITIONS:</b>	Mre11 monoclonal antibody can be stored at 4°C, stable for one year. As with all antibodies care should be taken to avoid repeated freeze thaw cycles. Antibodies should not be exposed to prolonged high temperatures.
<b>CLONALITY:</b>	Monoclonal
<b>ISOTYPE:</b>	IgG1/kappa
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	C19orf62, MERIT40, NBA1, HSPC142, BRISC and BRCA1-A complex member 1, Mediator of RAP80 interactions and targeting subunit of 40 kDa
<b>ACCESSION NO.:</b>	NP_001028721.1
<b>PROTEIN GI NO.:</b>	75709194
<b>OFFICIAL SYMBOL:</b>	BABAM1
<b>GENE ID:</b>	29086

### Background

FOR RESEARCH USE ONLY

December 13, 2016