



EAPII Antibody

CATALOG NUMBER: 47-137

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Synthetic peptide corresponding to aa residues 11-28 of human EAPII conjugated to KLH at the C-terminus.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity chroma-tography
PHYSICAL STATE:	Liquid
BUFFER:	PBS
STORAGE CONDITIONS:	EAPII antibody can be stored at 4°C, stable for one year. As with all antibodies care should be taken to avoid repeated freeze thaw cycles. Antibodies should not be exposed to prolonged high temperatures.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	PCANAP6, PRST, Solute carrier family 45 member 3, Prostate cancer-associated protein 6, IPCA6, IPCA-2, IPCA-6, IPCA-8, PCANAP2, PCANAP8
ACCESSION NO.:	NP_149093.1
PROTEIN GI NO.:	14916437
OFFICIAL SYMBOL:	SLC45A3
GENE ID:	85414

Background

BACKGROUND:	ETS proteins constitute a family of conserved sequence-specific DNA-binding proteins and function as transcription factors with roles in differentiation, lymphoid cell develop-ment, invasiveness, and angiogenesis. A novel ETS1 interacting protein designated as ETS1-associated protein II (EAPII) interacts with ETS1 and other ETS proteins (ETS2 and FLI1) and is a novel ETS1 modulator.
--------------------	---

FOR RESEARCH USE ONLY

December 13, 2016