




FGFR2 Antibody [1G3]

CATALOG NUMBER: 51-704



Immunohistochemistry of human skin tissue stained using FGFR2 Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	FGFR2 antibody can be used in Western Blot starting at 1 - 3 ug/mL, and immunohistochemistry starting at 10 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant protein
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
CONCENTRATION:	1 mg/ml
STORAGE CONDITIONS:	FGFR2 antibody can be stored short term 4 °C. For long term storage aliquot and store at -20 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2b,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	FGFR2, BEK, BBDS, Bacteria-expressed kinase, CD332 antigen, CFD1, Craniofacial dysostosis 1, CEK3, Fgf bek, FGF receptor, Hydroxyaryl-protein kinase, Jackson-Weiss syndrome, JWS, FGF Receptor 2, KSAM, KGFR, Soluble FGFR4 variant 4, BFR-1, TK14, TK25, CD332, ECT1, K-SAM
ACCESSION NO.:	P21802
PROTEIN GI NO.:	120049
OFFICIAL SYMBOL:	FGFR2

Background

FOR RESEARCH USE ONLY

December 13, 2016