MATERIAL SAFETY DATA SHEET

according to the Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 08/02/2012 Version 1.1

SECTION 1. Identification

Product identifier

Product number	170398
Product name	IC Multi-element standard I F^- = 100 mg/l, Cl^- = 250 mg/l, NO_3^-, SO_4^{2-} = 500 mg/l, PO_4^{3-} = 1000 mg/l in H_2O CertiPUR®

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Reagent for analysis

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation | 290 Concord Road, Billerica, MA 01821, United States of America | SDS Phone Support: +1-978-715-1335 | General Inquiries: +1-978-751-4321 | Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5) e-mail: mm_sds@merckgroup.com
Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week

SECTION 2. Hazards identification

GHS-Labeling

Not a hazardous substance or mixture according to Regulation (EC) No 1272/2008.

OSHA Hazards

While this material is not considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200), this MSDS contains valuable information critical to the safe handling and proper use of the product. This MSDS should be retained and available for employees and other users of this product.

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Chemical nature	Aqueous solution
Remarks	No hazardous ingredients according to the OSHA Hazard Communication Standard 29CFR 19101200.

SECTION 4. First aid measures

Description of first-aid measures

Inhalation
After inhalation: fresh air.

Skin contact
After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eye contact
After eye contact: rinse out with plenty of water.

Ingestion
After swallowing: make victim drink water (two glasses at most). Consult doctor if feeling unwell.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

irritant effects

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media
Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media
For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Not combustible.
Ambient fire may liberate hazardous vapors.

Advice for firefighters

Special protective equipment for fire-fighters
In the event of fire, wear self-contained breathing apparatus.

Further information
none

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Do not breathe vapors, aerosols. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

No special precautionary measures necessary.

Methods and materials for containment and cleaning up

Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent material (e.g. Chemizorb®). Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Ingredients

Basis	Value	Threshold limits	Remarks
sulphuric acid 7664-93-9			
ACGIH	Time Weighted Average (TWA):	0.2 mg/m³	Form of exposure: Thoracic fraction.
NIOSH/GUIDE	Recommended exposure limit (REL):	1 mg/m³	
OSHA_TRANS	PEL:	1 mg/m³	
Z1A	Time Weighted Average (TWA):	1 mg/m³	

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Change contaminated clothing. Wash hands after working with substance.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Recommended:

full contact:

Glove material:	Nitrile rubber
Glove thickness:	0.11 mm

Break through time: > 480 min

splash contact:

Glove material: Nitrile rubber
Glove thickness: 0.11 mm
Break through time: > 480 min

Respiratory protection
required when vapors/aerosols are generated.
Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	liquid
Color	colorless
Odor	odorless
Odor Threshold	No information available.
pH	ca. 1.5 at 68 °F (20 °C)
Melting point	No information available.
Boiling point	No information available.
Flash point	No information available.
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapor pressure	No information available.
Relative vapor density	No information available.
Relative density	1.000 g/cm³ at 68 °F (20 °C)
Water solubility	No information available.
Partition coefficient: n-octanol/water	No information available.

Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.

SECTION 10. Stability and reactivity

Reactivity
See below

Chemical stability
The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions
Violent reactions possible with:
The generally known reaction partners of water.

Conditions to avoid
no information available

Incompatible materials
no information available

Hazardous decomposition products
no information available

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure
Eye contact, Skin contact

Skin irritation
slight irritation

Eye irritation
slight irritation

Specific target organ systemic toxicity - single exposure
The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure
The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard
Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

Quantitative data on the toxicity of this product are not available.
Further toxicological data:
Hazardous properties cannot be excluded but are unlikely when the product is handled appropriately.
Further data:
Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

No information available.

Mobility in soil

No information available.

Other adverse effects

Additional ecological information
Biological effects:
Harmful effect due to pH shift.
No ecological problems are to be expected when the product is handled and used with due care and attention.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

UN number	UN 3264
Proper shipping name	CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S. (CONT. NITRIC ACID NOT MORE THAN 5%, SULPHURIC ACID)
Class	8
Packing group	III
Environmentally hazardous	--

Air transport (IATA)

UN number	UN 3264
Proper shipping name	CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S. (CONT. NITRIC ACID, SULPHURIC ACID)
Class	8
Packing group	III
Environmentally hazardous	--
Special precautions for user	no

Sea transport (IMDG)

UN number	UN 3264
Proper shipping name	CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S. (CONT. NITRIC ACID NOT MORE THAN 5%, SULPHURIC ACID)
Class	8
Packing group	III
Environmentally hazardous	--
Special precautions for user	yes

EmS F-A S-B

SECTION 15. Regulatory information

United States of America

OSHA Hazards

No OSHA Hazards

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

No SARA Hazards

US State Regulations

Massachusetts Right To Know

Ingredients
sulphuric acid
nitric acid
hydrochloric acid
Hydrofluoric acid

Pennsylvania Right To Know

Ingredients
water

New Jersey Right To Know

Ingredients
water

California Prop 65 Components

WARNING: this product contains a chemical known in the State of California to cause cancer.
Ingredients
sulphuric acid

Notification status

TSCA:	On TSCA Inventory
DSL:	All components of this product are on the Canadian DSL list.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.