




BID Antibody [1H11]

CATALOG NUMBER: 51-837



Immunohistochemistry of human thymus tissue stained using BID Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	IHC, WB
APPLICATIONS:	BID antibody can be used in ELISA, Western Blot, and immunohistochemistry starting at 2.5 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Human BID
HOST SPECIES:	Rat

Properties

PURIFICATION:	Affinity Purified
PHYSICAL STATE:	Liquid
BUFFER:	Aqueous buffer, 0.09% sodium azide, contains stabilizer if necessary
STORAGE CONDITIONS:	Store BID antibody at 4 °C. As with all antibodies avoid freeze/thaw cycles
CLONALITY:	Monoclonal
ISOTYPE:	IgG1
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	BID, Apoptic death agonist, BID isoform L(2), BID isoform Si6, Bh3, FP497, p22 BID, BID isoform ES(1b), Desmocollin type 4, Human BID coding sequence
ACCESSION NO.:	P55957
PROTEIN GI NO.:	2493285
OFFICIAL SYMBOL:	BID
GENE ID:	637

Background

