




Cyclin H Antibody [1B8]

CATALOG NUMBER: 51-897



Immunohistochemistry of human testis tissue stained using Cyclin H Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IF, IHC, WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	CCNH (AAH05280, 1 a.a. ~ 110 a.a) partial recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	Aliquot and store Cyclin H antibody at -20 °C or -80 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CCNH, Cyclin H, p34, p37, CAK, CAK complex subunit, Cyclin-H, MO15-associated protein
ACCESSION NO.:	P51946
PROTEIN GI NO.:	1706232
OFFICIAL SYMBOL:	CCNH
GENE ID:	902

Background

FOR RESEARCH USE ONLY

