



MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 08/22/2013

Version 1.1

SECTION 1. Identification

Product identifier

Product number	801068
Product name	Aluminium bromide anhydrous for synthesis

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Chemical for synthesis
-----------------	------------------------

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821, United States of America SDS Phone Support: +1-978-715-1335 General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)
---------	---

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

SECTION 2. Hazards identification

GHS Classification

Acute toxicity, Category 4, Oral, H302
Skin corrosion, Category 1B, H314
Corrosive to Metals, Category 1, H290

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word

Danger

Hazard Statements

H290 May be corrosive to metals.
H302 Harmful if swallowed.
H314 Causes severe skin burns and eye damage.

Precautionary Statements

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 801068
Product name Aluminium bromide anhydrous for synthesis

Version 1.1

P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
P301 + P330 + P331 IF SWALLOWED: rinse mouth. Do NOT induce vomiting.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P309 + P310 IF exposed or if you feel unwell: Immediately call a POISON CENTER or doctor/physician.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula	AlBr ₃	AlBr ₃ (Hill)
CAS-No.	7727-15-3	
Molar mass	266.69 g/mol	

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

aluminum bromide (>= 90 % - <= 100 %)

7727-15-3

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air. Call in physician.

Skin contact

After skin contact: wash off with plenty of water. Immediately remove contaminated clothing. If available swab with polyethylene glycol 400. Get medical attention.

Eye contact

After eye contact: rinse out with plenty of water. Immediately call in ophthalmologist.

Ingestion

After swallowing: make victim drink water (two glasses at most), avoid vomiting (risk of perforation!). Call a physician immediately. Do not attempt to neutralize.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

Irritation and corrosion, Cough, Shortness of breath, Unconsciousness, Diarrhea, Vomiting

The following applies to aluminum compounds in general: After swallowing: only slightly absorbable via the gastrointestinal tract. Serious disorders in man (from about 4000 mg aluminum up): phosphate metabolism, calcium metabolism.

The following applies to inorganic bromides in general: the uptake of large quantities as a result of misuse or improper handling leads to tiredness, agitation, spasms.

Risk of blindness!

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

801068

Version 1.1

Product name

Aluminium bromide anhydrous for synthesis

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Carbon dioxide (CO₂), Dry powder

Unsuitable extinguishing media

Water, Foam

Special hazards arising from the substance or mixture

Not combustible.

Ambient fire may liberate hazardous vapors.

Fire may cause evolution of:

hydrogen bromide

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid substance contact. Avoid inhalation of dusts.

Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up dry. Dispose of properly. Clean up affected area. Avoid generation of dusts.

SECTION 7. Handling and storage

Precautions for safe handling

Keep workplace dry. Do not allow product to come into contact with water.

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed. Dry.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

801068

Version 1.1

Product name

Aluminium bromide anhydrous for synthesis

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Ingredients

Basis	Value	Threshold limits	Remarks
<i>aluminum bromide 7727-15-3</i>			
ACGIH	Time Weighted Average (TWA):	1 mg/m ³	Form of exposure: Respirable fraction.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection

Tightly fitting safety goggles

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

protective clothing

Respiratory protection

required when dusts are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	crystals
Color	beige
Odor	stinging
Odor Threshold	No information available.
pH	No information available.
Melting point	97 °C

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	801068	Version 1.1
Product name	Aluminium bromide anhydrous for synthesis	

Boiling point/boiling range	482 - 518 °F (250 - 270 °C) at 1,013 hPa
Flash point	No information available.
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapor pressure	1.3 hPa at 178 °F (81 °C)
Relative vapor density	No information available.
Relative density	3.2 g/cm ³ at 68 °F (20 °C)
Water solubility	at 68 °F (20 °C) (rigorous decomposition)
Partition coefficient: n-octanol/water	No information available.
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.
Explosive properties	No information available.
Corrosion	May be corrosive to metals.

SECTION 10. Stability and reactivity

Reactivity

See below

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions

A risk of explosion and/or of toxic gas formation exists with the following substances:

Water, dichloromethane, Potassium, sodium, alkalines, Alcohols, Strong oxidizing agents, acids

Conditions to avoid

Exposure to moisture.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

801068

Version 1.1

Product name

Aluminium bromide anhydrous for synthesis

Incompatible materials

Metals

Hazardous decomposition products

in the event of fire: See section 5.

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Eye contact, Skin contact, Ingestion

Target Organs

Skin

Respiratory system

Acute oral toxicity

LD50 rat: 1,598 mg/kg (RTECS)

Symptoms: If ingested, severe burns of the mouth and throat, as well as a danger of perforation of the esophagus and the stomach.

Acute inhalation toxicity

Symptoms: burns of mucous membranes, Cough, Shortness of breath, Inhalation may lead to the formation of oedemas in the respiratory tract., Possible damages:, damage of respiratory tract

Corrosive to respiratory system

Skin irritation

Causes skin burns.

Causes burns.

Eye irritation

Causes eye burns.

Causes serious eye damage.

Risk of blindness!

Sensitization

Sensitization possible in predisposed persons.

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC

No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

OSHA

No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

801068

Version 1.1

Product name

Aluminium bromide anhydrous for synthesis

	carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

Decomposition of the substance with tissue moisture.

Systemic effects:

Vomiting, Diarrhea, Unconsciousness

Other information

The following applies to aluminum compounds in general: After swallowing: only slightly absorbable via the gastrointestinal tract. Serious disorders in man (from about 4000 mg aluminum up): phosphate metabolism, calcium metabolism.

The following applies to inorganic bromides in general: the uptake of large quantities as a result of misuse or improper handling leads to tiredness, agitation, spasms.

Further data:

Other dangerous properties can not be excluded.

Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

No information available.

Mobility in soil

No information available.

Additional ecological information

We have no quantitative data concerning the ecological effects of this product.

Biological effects:

Product reacts with water.

Further information on ecology

Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

801068

Version 1.1

Product name

Aluminium bromide anhydrous for synthesis

SECTION 14. Transport information

Land transport (DOT)

UN number	UN 1725
Proper shipping name	ALUMINIUM BROMIDE, ANHYDROUS
Class	8
Packing group	II
Environmentally hazardous	--

Air transport (IATA)

UN number	UN 1725
Proper shipping name	ALUMINIUM BROMIDE, ANHYDROUS
Class	8
Packing group	II
Environmentally hazardous	--
Special precautions for user	yes
IATA (Passenger)	Not permitted for transport

Sea transport (IMDG)

UN number	UN 1725
Proper shipping name	ALUMINIUM BROMIDE, ANHYDROUS
Class	8
Packing group	II
Environmentally hazardous	--
Special precautions for user	yes
EmS	F-A S-B

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Harmful if swallowed.
Corrosive to skin
Corrosive to eyes
Corrosive by inhalation.
Target organ effects

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Acute Health Hazard
Chronic Health Hazard

SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

801068

Version 1.1

Product name

Aluminium bromide anhydrous for synthesis

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

DEA List I

Not listed

DEA List II

Not listed

US State Regulations

Massachusetts Right To Know

Remarks

No components are subject to the Massachusetts Right to Know Act.

Pennsylvania Right To Know

Ingredients

aluminum bromide

New Jersey Right To Know

Ingredients

aluminum bromide

California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

Notification status

TSCA:

All components of the product are listed in the TSCA-inventory.

DSL:

All components of this product are on the Canadian DSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

801068

Version 1.1

Product name

Aluminium bromide anhydrous for synthesis

Full text of H-Statements referred to under sections 2 and 3.

H290

May be corrosive to metals.

H302

Harmful if swallowed.

H314

Causes severe skin burns and eye damage.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Revision Date 08/22/2013

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.