



NDRG4 Antibody [2G3]

CATALOG NUMBER: 70-107

Specifications

SPECIES REACTIVITY:	Human, Mouse
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	NDRG4 Monoclonal Antibody can be used for immunohistochemistry (tested on parafin embedded tissues) starting at 1:100 and Western Blot starting at 1:500 - 1:1000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Insect cell derived recombinant Human sIL-2Ralpha.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	NDRG4 Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	NDRG4, BDM1, KIAA1180, NDRG family member 4, SMAP8, SMAP-8, Protein NDRG4
ACCESSION NO.:	Q9ULP0
PROTEIN GI NO.:	20141614
OFFICIAL SYMBOL:	NDRG4
GENE ID:	65009

Background

FOR RESEARCH USE ONLY

December 13, 2016