



MHC Class II Antibody [TDR31.1]

CATALOG NUMBER: 70-203

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	FACS, IHC, WB
APPLICATIONS:	MHC Class II Monoclonal Antibody can be used for immunohistochemistry (tested on parafin embedded tissues) starting at 10 ug/mL.
USER NOTE:	Do not freeze
SPECIFICITY:	Monomorphic class II beta chain epitope.
IMMUNOGEN:	Purified (With Antibiotics) class II from JY cell line.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	50 mM sodium phosphate, pH 7.5, 100 mM potassium chloride, 150 mM sodium chloride, 0.5 mg/ml Gentamicin sulfate
STORAGE CONDITIONS:	MHC Class II Monoclonal antibody may be stored at Store at +4°C. Do not freeze.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	HLA-DP1B, HLA class II histocompatibility antigen, DP beta 1 chain, MHC class II antigen DPB1DPB1, HLA-DP, HLA-DPB
ACCESSION NO.:	P04440
PROTEIN GI NO.:	122263
OFFICIAL SYMBOL:	HLA-DPB1
GENE ID:	3115

Background

FOR RESEARCH USE ONLY

December 13, 2016