SAFETY DATA SHEET

Creation Date 27-Apr-2009 **Revision Date** 26-May-2017 **Revision Number** 4

1. Identification

Product Name **Methanol**

Cat No. : **AC615130000; AC615130025**

Synonyms Methyl alcohol

Recommended Use Laboratory chemicals.
Uses advised against Not for food, drug, pesticide or biocidal product use

Details of the supplier of the safety data sheet

Company
Fisher Scientific
One Reagent Lane
Fair Lawn, NJ 07410
Tel: (201) 796-7100

Acros Organics
One Reagent Lane
Fair Lawn, NJ 07410

Emergency Telephone Number
For information **US** call: 001-800-ACROS-01 / **Europe** call: +32 14 57 52 11
Emergency Number **US:**001-201-796-7100 / **Europe:** +32 14 57 52 99
CHEMTREC Tel. No.**US:**001-800-424-9300 / **Europe:**001-703-527-3887

2. Hazard(s) identification

Classification
This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Flammable liquids	Category 2
Acute oral toxicity	Category 3
Acute dermal toxicity	Category 3
Acute Inhalation Toxicity - Vapors	Category 3
Specific target organ toxicity (single exposure)	Category 1
Target Organs - Optic nerve.	
Specific target organ toxicity - (repeated exposure)	Category 1
Target Organs - Kidney, Liver, spleen, Blood.	

Label Elements

Signal Word
Danger

Hazard Statements
Highly flammable liquid and vapor
Toxic if swallowed
Toxic in contact with skin
Toxic if inhaled
Causes damage to organs
Causes damage to organs through prolonged or repeated exposure



Precautionary Statements
Prevention
Wash face, hands and any exposed skin thoroughly after handling
Do not eat, drink or smoke when using this product
Wear protective gloves/protective clothing/eye protection/face protection
Use only outdoors or in a well-ventilated area
Do not breathe dust/fume/gas/mist/vapors/spray
Keep away from heat/sparks/open flames/hot surfaces. - No smoking
Keep container tightly closed
Ground/bond container and receiving equipment
Use explosion-proof electrical/ventilating/lighting/equipment
Use only non-sparking tools
Take precautionary measures against static discharge
Keep cool
Response
IF exposed: Call a POISON CENTER or doctor/physician
Inhalation
IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing
Call a POISON CENTER or doctor/physician
Skin
Call a POISON CENTER or doctor/physician if you feel unwell
Wash contaminated clothing before reuse
IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower
Ingestion
IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician
Rinse mouth
Fire
In case of fire: Use CO2, dry chemical, or foam for extinction
Storage
Store locked up
Store in a well-ventilated place. Keep container tightly closed
Disposal
Dispose of contents/container to an approved waste disposal plant
Hazards not otherwise classified (HNOC)

Other hazards
Poison, may be fatal or cause blindness if swallowed. Vapor harmful. Cannot be made non-poisonous.
WARNING! This product contains a chemical known in the State of California to cause birth defects or other reproductive harm.

3. Composition / information on ingredients

Component	CAS-No	Weight %
Methyl alcohol	67-56-1	>95

4. First-aid measures

General Advice Immediate medical attention is required. Show this safety data sheet to the doctor in attendance.

Eye Contact Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

Immediate medical attention is required.

Skin Contact Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

Inhalation Move to fresh air. If breathing is difficult, give oxygen. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Immediate medical attention is required.

Ingestion Do not induce vomiting. Call a physician or Poison Control Center immediately.

Most important symptoms/effects Breathing difficulties. May cause blindness: Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting

Notes to Physician Treat symptomatically

5. Fire-fighting measures

Suitable Extinguishing Media Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide. Cool closed containers exposed to fire with water spray.

Unsuitable Extinguishing Media Water may be ineffective

Flash Point 12 °C / 53.6 °F

Method - No information available

Autoignition Temperature 455 °C / 851 °F

Explosion Limits

Upper 31.00 vol %
Lower 6.0 vol %
Sensitivity to Mechanical Impact No information available
Sensitivity to Static Discharge No information available

Specific Hazards Arising from the Chemical
Flammable. Risk of ignition. Vapors may form explosive mixtures with air. Vapors may travel to source of ignition and flash back. Containers may explode when heated. Vapors may form explosive mixtures with air.

Hazardous Combustion Products
Carbon monoxide (CO) Formaldehyde
Protective Equipment and Precautions for Firefighters
As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

NFPA

Health	Flammability	Instability	Physical hazards
1	3	0	N/A

6. Accidental release measures

Personal Precautions Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak. Use personal protective equipment. Ensure adequate ventilation. Remove all sources of ignition. Take precautionary measures against static discharges.

Environmental Precautions Should not be released into the environment. See Section 12 for additional ecological information.

Methods for Containment and Clean Up Soak up with inert absorbent material. Keep in suitable, closed containers for disposal. Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment.

7. Handling and storage

Handling Wear personal protective equipment. Do not breathe vapors or spray mist. Do not get in eyes, on skin, or on clothing. Use only under a chemical fume hood. Do not ingest. Keep away from open flames, hot surfaces and sources of ignition. Use only non-sparking tools. To avoid ignition of vapors by static electricity discharge, all metal parts of the equipment must be grounded. Take precautionary measures against static discharges.

Storage Keep container tightly closed in a dry and well-ventilated place. Keep away from open flames, hot surfaces and sources of ignition. Flammables area.

8. Exposure controls / personal protection

Exposure Guidelines

Component	ACGIH TLV	OSHA PEL	NIOSH IDLH	Mexico OEL (TWA)
Methyl alcohol	TWA: 200 ppm STEL: 250 ppm Skin	(Vacated) TWA: 200 ppm (Vacated) TWA: 260 mg/m^3 (Vacated) STEL: 250 ppm (Vacated) STEL: 325 mg/m^3 Skin TWA: 200 ppm TWA: 260 mg/m^3	IDLH: 6000 ppm TWA: 200 ppm TWA: 260 mg/m^3 STEL: 250 ppm STEL: 325 mg/m^3	TWA: 200 ppm TWA: 260 mg/m^3 STEL: 250 ppm STEL: 310 mg/m^3

Legend

ACGIH - American Conference of Governmental Industrial Hygienists
OSHA - Occupational Safety and Health Administration
NIOSH IDLH: The National Institute for Occupational Safety and Health Immediately Dangerous to Life or Health

Engineering Measures Use only under a chemical fume hood. Use explosion-proof electrical/ventilating/lighting/equipment. Ensure that eyewash stations and safety showers are close to the workstation location.

Personal Protective Equipment

Eye/face Protection Wear appropriate protective eyeglasses or chemical safety goggles as described by OSHA's eye and face protection regulations in 29 CFR 1910.133 or European Standard EN166.

Skin and body protection Wear appropriate protective gloves and clothing to prevent skin exposure.

Respiratory Protection Follow the OSHA respirator regulations found in 29 CFR 1910.134 or European Standard EN 149. Use a NIOSH/MSHA or European Standard EN 149 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.

Hygiene Measures When using, do not eat, drink or smoke. Provide regular cleaning of equipment, work area and clothing.

9. Physical and chemical properties

Physical State	Liquid
Appearance	Colorless
Odor	Alcohol-like
Odor Threshold	No information available
pH	Not applicable
Melting Point/Range	-98 °C / -144.4 °F
Boiling Point/Range	64.7 °C / 148.5 °F @ 760 mmHg
Flash Point	12 °C / 53.6 °F
Evaporation Rate	5.2 (ether = 1)
Flammability (solid,gas)	Not applicable
Flammability or explosive limits	
Upper	31.00 vol %

Lower	6.0 vol %
Vapor Pressure	128 hPa @ 20 °C
Vapor Density	1.11
Specific Gravity	0.791
Solubility	Miscible with water
Partition coefficient; n-octanol/water	No data available
Autoignition Temperature	455 °C / 851 °F
Decomposition Temperature	No information available
Viscosity	0.55 cP at 20 °C
Molecular Formula	C H4 O
Molecular Weight	32.04
VOC Content(%)	100
Surface tension	0.02255 N/m @ 20°C

10. Stability and reactivity

Reactive Hazard None known, based on information available

Stability Stable under normal conditions.

Conditions to Avoid Incompatible products. Heat, flames and sparks. Keep away from open flames, hot surfaces and sources of ignition.

Incompatible Materials Strong oxidizing agents, Strong acids, Acid anhydrides, Acid chlorides, Strong bases, Metals, Peroxides

Hazardous Decomposition Products Carbon monoxide (CO), Formaldehyde

Hazardous Polymerization Hazardous polymerization does not occur.

Hazardous Reactions None under normal processing.

11. Toxicological information

Acute Toxicity

Product Information

Component Information

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Methyl alcohol	**Calc. ATE 60 mg/kg** LD50 > 1187 – 2769 mg/kg (Rat)	**Calc. ATE 60 mg/kg** LD50 = 17100 mg/kg (Rabbit)	**Calc. ATE 0.6 mg/L (vapours) or 0.5 mg/L (mists)** LC50 = 128.2 mg/L (Rat) 4 h

Toxicologically Synergistic Products Carbon tetrachloride

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Irritation May cause skin and eye irritation

Sensitization No information available

Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen.

Component	CAS-No	IARC	NTP	ACGIH	OSHA	Mexico
Methyl alcohol	67-56-1	Not listed	Not listed	Not listed	Not listed	Not listed

Mutagenic Effects No information available

Reproductive Effects No information available.

Developmental Effects Component substance is listed on California Proposition 65 as a developmental hazard.

Teratogenicity No information available.

STOT - single exposure Optic nerve
STOT - repeated exposure Kidney Liver spleen Blood

Aspiration hazard No information available

Symptoms / effects,both acute and delayed May cause blindness: Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting

Endocrine Disruptor Information No information available

Other Adverse Effects The toxicological properties have not been fully investigated.

12. Ecological information

Ecotoxicity

.

Component	Freshwater Algae	Freshwater Fish	Microtox	Water Flea
Methyl alcohol	Not listed	Pimephales promelas: LC50 > 10000 mg/L 96h	EC50 = 39000 mg/L 25 min EC50 = 40000 mg/L 15 min EC50 = 43000 mg/L 5 min	EC50 > 10000 mg/L 24h

Persistence and Degradability Persistence is unlikely based on information available.

Bioaccumulation/ Accumulation No information available.

Mobility Will likely be mobile in the environment due to its volatility.

Component	log Pow
Methyl alcohol	-0.74

13. Disposal considerations

Waste Disposal Methods Should not be released into the environment.

Component	RCRA - U Series Wastes	RCRA - P Series Wastes
Methyl alcohol - 67-56-1	U154	-

14. Transport information

DOT

UN-No UN1230
Proper Shipping Name METHANOL
Hazard Class 3
Packing Group II

TDG

UN-No UN1230
Proper Shipping Name METHANOL
Hazard Class 3
Subsidiary Hazard Class 6.1
Packing Group II

IATA

UN-No UN1230
Proper Shipping Name METHANOL
Hazard Class 3
Subsidiary Hazard Class 6.1
Packing Group II

IMDG/IMO

UN-No UN1230
Proper Shipping Name METHANOL
Hazard Class 3
Subsidiary Hazard Class 6.1

Packing Group II

15. Regulatory information

International Inventories

Component	TSCA	DSL	NDSL	EINECS	ELINCS	NLP	PICCS	ENCS	AICS	IECSC	KECL
Methyl alcohol	X	X	-	200-659-6	-		X	X	X	X	X

Legend:
X - Listed
E - Indicates a substance that is the subject of a Section 5(e) Consent order under TSCA.
F - Indicates a substance that is the subject of a Section 5(f) Rule under TSCA.
N - Indicates a polymeric substance containing no free-radical initiator in its inventory name but is considered to cover the designated polymer made with any free-radical initiator regardless of the amount used.
P - Indicates a commenced PMN substance
R - Indicates a substance that is the subject of a Section 6 risk management rule under TSCA.
S - Indicates a substance that is identified in a proposed or final Significant New Use Rule
T - Indicates a substance that is the subject of a Section 4 test rule under TSCA.
XU - Indicates a substance exempt from reporting under the Inventory Update Rule, i.e. Partial Updating of the TSCA Inventory Data Base Production and Site Reports (40 CFR 710(B).
Y1 - Indicates an exempt polymer that has a number-average molecular weight of 1,000 or greater.
Y2 - Indicates an exempt polymer that is a polyester and is made only from reactants included in a specified list of low concern reactants that comprises one of the eligibility criteria for the exemption rule.

U.S. Federal Regulations

TSCA 12(b) Not applicable

SARA 313

Component	CAS-No	Weight %	SARA 313 - Threshold Values %
Methyl alcohol	67-56-1	>95	1.0

SARA 311/312 Hazard Categories

Acute Health Hazard	Yes
Chronic Health Hazard	Yes
Fire Hazard	Yes
Sudden Release of Pressure Hazard	No
Reactive Hazard	No

CWA (Clean Water Act) Not applicable

Clean Air Act

Component	HAPS Data	Class 1 Ozone Depletors	Class 2 Ozone Depletors
Methyl alcohol	X		-

OSHA Occupational Safety and Health Administration
Not applicable

CERCLA
This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

Component	Hazardous Substances RQs	CERCLA EHS RQs
Methyl alcohol	5000 lb	-

California Proposition 65 This product contains the following proposition 65 chemicals

Component	CAS-No	California Prop. 65	Prop 65 NSRL	Category
Methyl alcohol	67-56-1	Developmental	-	Developmental

U.S. State Right-to-Know Regulations

Component	Massachusetts	New Jersey	Pennsylvania	Illinois	Rhode Island

Methyl alcohol	X	X	X	X	X

U.S. Department of Transportation

Reportable Quantity (RQ): Y
DOT Marine Pollutant N
DOT Severe Marine Pollutant N

U.S. Department of Homeland Security
This product does not contain any DHS chemicals.

Other International Regulations

Mexico - Grade Serious risk, Grade 3

16. Other information

Prepared By
Regulatory Affairs
Thermo Fisher Scientific
Email: EMSDS.RA@thermofisher.com

Creation Date 27-Apr-2009
Revision Date 26-May-2017
Print Date 26-May-2017
Revision Summary This document has been updated to comply with the US OSHA HazCom 2012 Standard replacing the current legislation under 29 CFR 1910.1200 to align with the Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

Disclaimer
The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of SDS