



TF Antibody, Monoclonal

CATALOG NUMBER: 70-205

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	IHC, WB
APPLICATIONS:	TF Monoclonal Antibody can be used for immunohistochemistry (tested on parafin embedded tissues) starting at 1:25 and Western Blot starting at 1:5000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Protein purified from Human plasma.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Ammonium Sulfate Precipitation
PHYSICAL STATE:	Liquid
BUFFER:	HEPES with 0.15M NaCl, 0.01% BSA, 0.03% sodium azide, and 50% glycerol
STORAGE CONDITIONS:	TF Monoclonal antibody may be stored at May be stored at 4°C for short-term. Aliquot to avoid repeated freezing and thawing. Store at -20°C. Aliquots are stable for 12 months.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	TF, PRO1557, Serotransferrin, Siderophilin, TFQTL1, Beta-1 metal-binding globulin, Transferrin, PRO2086
ACCESSION NO.:	P02787
PROTEIN GI NO.:	313104271
OFFICIAL SYMBOL:	TF
GENE ID:	7018

Background

FOR RESEARCH USE ONLY

December 13, 2016