

SAFETY DATA SHEET

Creation Date 16-Jun-2009

Revision Date 26-May-2017

Revision Number 3

1. Identification

Product Name Acetonitrile

Cat No. : AC615140000; AC615140025

Synonyms AN; Methyl cyanide; Ethanenitrile

Recommended Use Laboratory chemicals.

Uses advised against Not for food, drug, pesticide or biocidal product use

Details of the supplier of the safety data sheet

Company

Fisher Scientific
One Reagent Lane
Fair Lawn, NJ 07410
Tel: (201) 796-7100

Acros Organics
One Reagent Lane
Fair Lawn, NJ 07410

Emergency Telephone Number

For information **US** call: 001-800-ACROS-01 / **Europe** call: +32 14 57 52 11

Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99

CHEMTREC Tel. No.**US**:001-800-424-9300 / **Europe**:001-703-527-3887

2. Hazard(s) identification

Classification

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Flammable liquids	Category 2
Acute oral toxicity	Category 4
Acute dermal toxicity	Category 4
Acute Inhalation Toxicity - Vapors	Category 4
Serious Eye Damage/Eye Irritation	Category 2

Label Elements

Signal Word

Danger

Hazard Statements

Highly flammable liquid and vapor
Harmful if swallowed
Harmful in contact with skin
Causes serious eye irritation
Harmful if inhaled

**Precautionary Statements****Prevention**

Wash face, hands and any exposed skin thoroughly after handling
Do not eat, drink or smoke when using this product
Wear protective gloves/protective clothing/eye protection/face protection
Use only outdoors or in a well-ventilated area
Do not breathe dust/fume/gas/mist/vapors/spray
Keep away from heat/sparks/open flames/hot surfaces. - No smoking
Keep container tightly closed
Ground/bond container and receiving equipment
Use explosion-proof electrical/ventilating/lighting/equipment
Use only non-sparking tools
Take precautionary measures against static discharge

Response

Get medical attention/advice if you feel unwell

Inhalation

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing
Call a POISON CENTER or doctor/physician if you feel unwell

Skin

Call a POISON CENTER or doctor/physician if you feel unwell
Wash contaminated clothing before reuse
IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower

Eyes

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
If eye irritation persists: Get medical advice/attention

Ingestion

IF SWALLOWED: Call a POISON CENTER or doctor/physician if you feel unwell
Rinse mouth

Fire

In case of fire: Use CO₂, dry chemical, or foam for extinction

Storage

Store in a well-ventilated place. Keep cool

Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

None identified

3. Composition / information on ingredients

Component	CAS-No	Weight %
Acetonitrile	75-05-8	>95

4. First-aid measures

General Advice

Immediate medical attention is required. Show this safety data sheet to the doctor in attendance.

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.
Immediate medical attention is required.

Skin Contact	Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.
Inhalation	Move to fresh air. If breathing is irregular or stopped, administer artificial respiration. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Immediate medical attention is required.
Ingestion	Do not induce vomiting. Call a physician or Poison Control Center immediately.
Most important symptoms/effects	Breathing difficulties. Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting: Metabolism may release cyanide, which may result in headache, dizziness, weakness, collapse, unconsciousness, and possible death: Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting
Notes to Physician	Treat symptomatically

5. Fire-fighting measures

Suitable Extinguishing Media	Water spray. CO ₂ , dry chemical, dry sand, alcohol-resistant foam. Cool closed containers exposed to fire with water spray.
Unsuitable Extinguishing Media	Water may be ineffective, Do not use a solid water stream as it may scatter and spread fire
Flash Point	12.8 °C / 55 °F
Method -	No information available
Autoignition Temperature	525 °C / 977 °F
Explosion Limits	
Upper	16 vol %
Lower	3 vol %
Oxidizing Properties	Not oxidising
Sensitivity to Mechanical Impact	No information available
Sensitivity to Static Discharge	No information available

Specific Hazards Arising from the Chemical

Flammable. Vapors may form explosive mixtures with air. Vapors may travel to source of ignition and flash back. Containers may explode when heated. Vapors may form explosive mixtures with air.

Hazardous Combustion Products

Hydrogen cyanide (hydrocyanic acid) Nitrogen oxides (NO_x) Carbon monoxide (CO) Carbon dioxide (CO₂)

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

NFPA

Health
2

Flammability
3

Instability
0

Physical hazards
N/A

6. Accidental release measures

Personal Precautions	Remove all sources of ignition. Take precautionary measures against static discharges. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak. Ensure adequate ventilation. Use personal protective equipment.
Environmental Precautions	Should not be released into the environment. See Section 12 for additional ecological information.
Methods for Containment and Clean	Remove all sources of ignition. Take precautionary measures against static discharges.

Up Provide adequate ventilation. Use spark-proof tools and explosion-proof equipment. Soak up with inert absorbent material. Keep in suitable, closed containers for disposal. Prevent product from entering drains.

7. Handling and storage

Handling Wear personal protective equipment. Ensure adequate ventilation. Keep away from open flames, hot surfaces and sources of ignition. Take precautionary measures against static discharges. Do not get in eyes, on skin, or on clothing. Do not breathe vapors or spray mist. Use spark-proof tools and explosion-proof equipment. Use only non-sparking tools. To avoid ignition of vapors by static electricity discharge, all metal parts of the equipment must be grounded.

Storage Keep container tightly closed in a dry and well-ventilated place. Keep away from heat and sources of ignition. Flammables area.

8. Exposure controls / personal protection

Exposure Guidelines

Component	ACGIH TLV	OSHA PEL	NIOSH IDLH	Mexico OEL (TWA)
Acetonitrile	TWA: 20 ppm Skin	(Vacated) TWA: 40 ppm (Vacated) TWA: 70 mg/m ³ (Vacated) TWA: 5 mg/m ³ (Vacated) STEL: 60 ppm (Vacated) STEL: 105 mg/m ³ TWA: 40 ppm TWA: 70 mg/m ³	IDLH: 500 ppm IDLH: 25 mg/m ³ TWA: 20 ppm TWA: 34 mg/m ³	TWA: 40 ppm TWA: 70 mg/m ³ TWA: 5 mg/m ³ STEL: 60 ppm STEL: 105 mg/m ³

Legend

ACGIH - American Conference of Governmental Industrial Hygienists

OSHA - Occupational Safety and Health Administration

NIOSH IDLH: The National Institute for Occupational Safety and Health Immediately Dangerous to Life or Health

Engineering Measures Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Use explosion-proof electrical/ventilating/lighting/equipment.

Personal Protective Equipment

Eye/face Protection Wear appropriate protective eyeglasses or chemical safety goggles as described by OSHA's eye and face protection regulations in 29 CFR 1910.133 or European Standard EN166.

Skin and body protection Wear appropriate protective gloves and clothing to prevent skin exposure.

Respiratory Protection Follow the OSHA respirator regulations found in 29 CFR 1910.134 or European Standard EN 149. Use a NIOSH/MSHA or European Standard EN 149 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.

Hygiene Measures When using, do not eat, drink or smoke. Provide regular cleaning of equipment, work area and clothing.

9. Physical and chemical properties

Physical State	Liquid
Appearance	Colorless
Odor	aromatic
Odor Threshold	170 ppm
pH	No information available

Melting Point/Range	-46 °C / -50.8 °F
Boiling Point/Range	81 - 82 °C / 177.8 - 179.6 °F @ 760 mmHg
Flash Point	12.8 °C / 55 °F
Evaporation Rate	5.79
Flammability (solid,gas)	Not applicable
Flammability or explosive limits	
Upper	16 vol %
Lower	3 vol %
Vapor Pressure	97 mbar @ 20 °C
Vapor Density	1.42
Specific Gravity	0.781
Solubility	miscible
Partition coefficient; n-octanol/water	No data available
Autoignition Temperature	525 °C / 977 °F
Decomposition Temperature	No information available
Viscosity	0.36 cP at 20 °C
Molecular Formula	C ₂ H ₃ N
Molecular Weight	41.05

10. Stability and reactivity

Reactive Hazard	None known, based on information available
Stability	Stable under normal conditions.
Conditions to Avoid	Incompatible products. Keep away from open flames, hot surfaces and sources of ignition. Exposure to moisture.
Incompatible Materials	Strong oxidizing agents, Strong acids, Reducing agents, Bases
Hazardous Decomposition Products	Hydrogen cyanide (hydrocyanic acid), Nitrogen oxides (NO _x), Carbon monoxide (CO), Carbon dioxide (CO ₂)
Hazardous Polymerization	Hazardous polymerization does not occur.
Hazardous Reactions	None under normal processing.

11. Toxicological information

Acute Toxicity

Product Information Component Information

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Acetonitrile	ATE = 617 mg/kg 450-787 mg/kg (Rat) 2460 mg/kg (Rat)	> 2000 mg/kg (Rabbit)	ATE = 3587 ppm 7551 ppm (Rat) 8 h

Toxicologically Synergistic Products No information available

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Irritation	Irritating to eyes
Sensitization	No information available
Carcinogenicity	The table below indicates whether each agency has listed any ingredient as a carcinogen.

Component	CAS-No	IARC	NTP	ACGIH	OSHA	Mexico
Acetonitrile	75-05-8	Not listed	Not listed	Not listed	Not listed	Not listed

Mutagenic Effects No information available

Reproductive Effects	No information available.
Developmental Effects	No information available.
Teratogenicity	No information available.
STOT - single exposure	None known
STOT - repeated exposure	None known
Aspiration hazard	No information available
Symptoms / effects, both acute and delayed	Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting: Metabolism may release cyanide, which may result in headache, dizziness, weakness, collapse, unconsciousness, and possible death: Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting
Endocrine Disruptor Information	No information available
Other Adverse Effects	The toxicological properties have not been fully investigated.

12. Ecological information

Ecotoxicity

Component	Freshwater Algae	Freshwater Fish	Microtox	Water Flea
Acetonitrile	Not listed	LC50: = 1650 mg/L, 96h static (Poecilia reticulata) LC50: = 1850 mg/L, 96h static (Lepomis macrochirus) LC50: = 1000 mg/L, 96h static (Pimephales promelas) LC50: 1600 - 1690 mg/L, 96h flow-through (Pimephales promelas)	EC50 = 28000 mg/L 48 h EC50 = 73 mg/L 24 h EC50 = 7500 mg/L 15 h	EC50: = 5838 mg/L, 18h (Daphnia pulex)

Persistence and Degradability Persistence is unlikely based on information available.

Bioaccumulation/ Accumulation No information available.

Mobility Will likely be mobile in the environment due to its volatility.

Component	log Pow
Acetonitrile	-0.34

13. Disposal considerations

Waste Disposal Methods Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Chemical waste generators must also consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.

Component	RCRA - U Series Wastes	RCRA - P Series Wastes
Acetonitrile - 75-05-8	U003	-

14. Transport information

DOT

UN-No	UN1648
Proper Shipping Name	ACETONITRILE
Hazard Class	3
Packing Group	II

TDG

UN-No UN1648
 Proper Shipping Name ACETONITRILE
 Hazard Class 3
 Packing Group II

IATA

UN-No UN1648
 Proper Shipping Name ACETONITRILE
 Hazard Class 3
 Packing Group II

IMDG/IMO

UN-No UN1648
 Proper Shipping Name ACETONITRILE
 Hazard Class 3
 Packing Group II

15. Regulatory information

All of the components in the product are on the following Inventory lists: X = listed

International Inventories

Component	TSCA	DSL	NDSL	EINECS	ELINCS	NLP	PICCS	ENCS	AICS	IECSC	KECL
Acetonitrile	X	X	-	200-835-2	-		X	X	X	X	X

Legend:

X - Listed

E - Indicates a substance that is the subject of a Section 5(e) Consent order under TSCA.

F - Indicates a substance that is the subject of a Section 5(f) Rule under TSCA.

N - Indicates a polymeric substance containing no free-radical initiator in its inventory name but is considered to cover the designated polymer made with any free-radical initiator regardless of the amount used.

P - Indicates a commenced PMN substance

R - Indicates a substance that is the subject of a Section 6 risk management rule under TSCA.

S - Indicates a substance that is identified in a proposed or final Significant New Use Rule

T - Indicates a substance that is the subject of a Section 4 test rule under TSCA.

XU - Indicates a substance exempt from reporting under the Inventory Update Rule, i.e. Partial Updating of the TSCA Inventory Data Base Production and Site Reports (40 CFR 710(B)).

Y1 - Indicates an exempt polymer that has a number-average molecular weight of 1,000 or greater.

Y2 - Indicates an exempt polymer that is a polyester and is made only from reactants included in a specified list of low concern reactants that comprises one of the eligibility criteria for the exemption rule.

U.S. Federal Regulations**TSCA 12(b)****SARA 313**

Component	CAS-No	Weight %	SARA 313 - Threshold Values %
Acetonitrile	75-05-8	>95	1.0

SARA 311/312 Hazard Categories

Acute Health Hazard	Yes
Chronic Health Hazard	Yes
Fire Hazard	Yes
Sudden Release of Pressure Hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

Component	CWA - Hazardous Substances	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants
Acetonitrile	-	-	X	X

Clean Air Act

Component	HAPS Data	Class 1 Ozone Depletors	Class 2 Ozone Depletors
-----------	-----------	-------------------------	-------------------------

Acetonitrile	X		-
--------------	---	--	---

OSHA Occupational Safety and Health Administration
Not applicable

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

Component	Hazardous Substances RQs	CERCLA EHS RQs
Acetonitrile	5000 lb	-

California Proposition 65 This product does not contain any Proposition 65 chemicals

U.S. State Right-to-Know Regulations

Component	Massachusetts	New Jersey	Pennsylvania	Illinois	Rhode Island
Acetonitrile	X	X	X	X	X

U.S. Department of Transportation

Reportable Quantity (RQ): N
DOT Marine Pollutant N
DOT Severe Marine Pollutant N

U.S. Department of Homeland Security

This product does not contain any DHS chemicals.

Other International Regulations

Mexico - Grade Serious risk, Grade 3

16. Other information

Prepared By Regulatory Affairs
Thermo Fisher Scientific
Email: EMSDS.RA@thermofisher.com

Creation Date 16-Jun-2009

Revision Date 26-May-2017

Print Date 26-May-2017

Revision Summary This document has been updated to comply with the US OSHA HazCom 2012 Standard replacing the current legislation under 29 CFR 1910.1200 to align with the Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of SDS