



VLDLR Antibody [1H10]

CATALOG NUMBER: 70-255

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	VLDLR Monoclonal Antibody can be used for immunohistochemistry (tested on paraffin embedded tissues) starting at 1:50.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Free human cardiac troponin I.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	IgG Fractionation
PHYSICAL STATE:	Liquid
BUFFER:	0.05M Sodium Phosphate; 0.1M NaCl; 1mM EDTA; pH 6.6
STORAGE CONDITIONS:	VLDLR Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	VLDLR, CARMQ1, CHRMQ1, VLDL receptor, VLDL-R, VLDLRCH
ACCESSION NO.:	P98155
PROTEIN GI NO.:	1730111
OFFICIAL SYMBOL:	VLDLR
GENE ID:	7436

Background

FOR RESEARCH USE ONLY

December 13, 2016