



ORM1 Antibody

CATALOG NUMBER: 70-545

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, IP, WB
APPLICATIONS:	ORM1 Antibody can be used for ELISA starting at 1:1350000, Immunohistochemistry in paraffin embedded tissues starting at 2.5 ug/mL, Immunoprecipitation and Western Blotting starting at 1:2000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Assay by immunoelectrophoresis resulted in a single precipitin arc against anti-rabbit serum as well as purified and partially purified a1-Acid Glycoprotein (Human Plasma) .
IMMUNOGEN:	A-1-Acid Glycoprotein (Human Plasma).
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Ion Exchange Chromatography
BUFFER:	PBS, pH 7.2, 0.01% sodium azide.
CONCENTRATION:	10 mg/ml
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	ORM1, AGP-A, Alpha-1-acid glycoprotein 1, AGP 1, AGP1, Alpha-1-acid glycoprotein 2, OMD 1, Orosomucoid, Orosomucoid-1, ORM, Orosomucoid 1
ACCESSION NO.:	P02763
PROTEIN GI NO.:	112877
OFFICIAL SYMBOL:	ORM1
GENE ID:	5004

Background

FOR RESEARCH USE ONLY

December 13, 2016