




CD91 Antibody [MA-5A6]

CATALOG NUMBER: 48-013



Human liver tissue stained with LRP1
Antibody at 10 ug/mL followed by
biotinylated anti-mouse IgG secondary
antibody, alkaline phosphatase-streptavidin
and chromogen.

Specifications

SPECIES REACTIVITY:	Human, Mouse
TESTED APPLICATIONS:	FACS, IHC, WB
APPLICATIONS:	CD91 antibody can be used in immunohistochemistry starting at 2.5 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	0.05 M sodium phosphate; 0.1 M sodium chloride; 1 mM EDTA; pH 6.6.
STORAGE CONDITIONS:	Store CD91 antibody at 4 °C or -20 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2b
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	LRP1, Apolipoprotein E receptor, CD91 antigen, CD91, A2MR, IGFBP3R, Alpha-2-macroglobulin receptor, TGFBR5, Type V tgf-beta receptor, APOER, APR, LRP, LRP-1
ACCESSION NO.:	Q07954
PROTEIN GI NO.:	317373384
OFFICIAL SYMBOL:	LRP1
GENE ID:	4035

Background

