




## ATIC Antibody [F38 P7 H9]

CATALOG NUMBER: 48-813



Immunohistochemistry staining of ATIC in spleen tissue using ATIC monoclonal Antibody.

### Specifications

<b>SPECIES REACTIVITY:</b>	Bovine, Dog, Drosophila, Gibbon, Gorilla, Horse, Human, Monkey, Orangutan, Pig, Xenopus
<b>TESTED APPLICATIONS:</b>	IHC, WB
<b>APPLICATIONS:</b>	ATIC antibody can be used in ELISA, and immunohistochemistry starting at 10 ug/mL.
<b>USER NOTE:</b>	<b>Do not freeze</b>
<b>IMMUNOGEN:</b>	ATIC monoclonal antibody was raised against a ovalbumin - conjugated synthetic peptide of ATIC (Human).
<b>HOST SPECIES:</b>	Mouse

### Properties

<b>PURIFICATION:</b>	Affinity Chromatography
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	Phosphate-buffered solution, pH 7.2, 0.09% sodium azide at 0.5 mg/ml.
<b>STORAGE CONDITIONS:</b>	Store ATIC antibody at 4 °C. <b>Do not freeze.</b>
<b>CLONALITY:</b>	Monoclonal
<b>ISOTYPE:</b>	IgG 1
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	ATIC, AICAR, AICARFT, IMPCHASE, PURH
<b>ACCESSION NO.:</b>	P31939
<b>PROTEIN GI NO.:</b>	23831360
<b>OFFICIAL SYMBOL:</b>	ATIC
<b>GENE ID:</b>	471

### Background

FOR RESEARCH USE ONLY

