
Product Specifications

VWR Part Number: IR1748
ImmunoReagents, Inc. Part Number: GtxHu-010-DBIO

Product: GOAT X HU IGG/A/M BIO 1VL

Concentration: 1.50 mg/ml (E 1% at 280 nm = 13.0)

Amount: 2.0 mg

Conjugate: Biotin (NHS-LC)

Form: Clear, colorless liquid

Purification: Affinity purified using solid phase Human IgA + IgG + IgM

Purity: Affinity purified antibody is > 95% based on SDS-PAGE

Host: Goat

Immunogen: Purified human IgG + IgA + IgM, whole molecule

Buffer: 10 mM Sodium Phosphate, 0.15 M Sodium Chloride, pH 7.2, 1 % (w/v) BSA,
Protease/IgG free

Storage: 2-8 °C

Shelf Life: 1 year from date of receipt. Prepare working dilution prior to use and then discard.

Specificity: Based on IEP, this antibody reacts with: · heavy chains on human IgA + IgG + IgM · light chains on all human immunoglobulins

Cross Reactivity: Based on IEP, no reactivity is observed to: · non-immunoglobulin human serum immunoglobulins

Country of Origin: Goat serum was obtained from healthy animals of US origin and under the care of a registered veterinarian.

Applications: This conjugate is suitable for immunomicroscopy and flow cytometry. The optimal working dilution should be determined by the investigator. Suggested starting dilution(?): · 1:20 - 1:2,000 for most applications

Disclaimer: For in vitro Laboratory Use Only. Not for diagnostic or therapeutic use. Not for human or animal consumption. Suggested applications of our products are not recommendations to use our products in violation of any patent or as a license under any patent of ImmunoReagents, Inc.

Product may not be resold or modified for resale without prior written approval of ImmunoReagents, Inc.