




DARS Antibody [2F11]

CATALOG NUMBER: 51-447



Immunohistochemistry of human brain
cortex tissue stained using DARS
Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, RNAi, WB
APPLICATIONS:	DARS antibody can be used in Western Blot, and immunohistochemistry starting at 5 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	DARS (NP_001340, 393 a.a. ~ 501 a.a) partial recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	Store DARS antibody at -20 °C. Aliquot to avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	DARS, Aspartyl-tRNA synthetase, AspRS
ACCESSION NO.:	P14868
PROTEIN GI NO.:	20178330
OFFICIAL SYMBOL:	DARS
GENE ID:	1615

Background

