




HMGB2 Antibody [3C7]

CATALOG NUMBER: 51-468



Immunohistochemistry of human placenta tissue stained using HMGB2 Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	HMGB2 antibody can be used in ELISA starting at 1:000 - 1:1000, and immunohistochemistry starting at 10 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	HMGB2 (AAH00903, 1 a.a. ~ 196 a.a) full length recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	Store HMGB2 antibody at -20 °C. Aliquot to avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	HMGB2, HMG-2, High mobility group box 2, High-mobility group box 2, HMG2, High mobility group protein 2, High mobility group protein B2
ACCESSION NO.:	P26583
PROTEIN GI NO.:	123374
OFFICIAL SYMBOL:	HMGB2
GENE ID:	3148

