



DBI Antibody [20B10]

CATALOG NUMBER: 70-222

Specifications

| | |
|-----------------------------|---|
| SPECIES REACTIVITY: | Human |
| TESTED APPLICATIONS: | ELISA, IHC, IP |
| APPLICATIONS: | DBI Monoclonal Antibody can be used for immunohistochemistry (tested on paraffin embedded tissues) starting at 1:200. |
| USER NOTE: | Optimal dilutions for each application to be determined by the researcher. |
| IMMUNOGEN: | Recombinant human GST-fusion protein purified from E. coli. |
| HOST SPECIES: | Mouse |

Properties

| | |
|----------------------------|---|
| PURIFICATION: | Ammonium Sulfate Precipitation |
| PHYSICAL STATE: | Liquid |
| BUFFER: | HEPES with 0.15M NaCl, 0.01% BSA, 0.03% sodium azide, and 50% glycerol |
| STORAGE CONDITIONS: | DBI Monoclonal antibody may be stored at 4°C; Avoid freeze-thaw cycles. |
| CLONALITY: | Monoclonal |
| ISOTYPE: | IgG1,k |
| CONJUGATE: | Unconjugated |

Additional Info

| | |
|-------------------------|---|
| ALTERNATE NAMES: | DBI, ACBP, Acyl-CoA-binding protein, CCK-RP, Diazepam-binding inhibitor, ACBD1, GABA receptor modulator, EP, Endozepine |
| ACCESSION NO.: | P07108 |
| PROTEIN GI NO.: | 118276 |
| OFFICIAL SYMBOL: | DBI |
| GENE ID: | 1622 |

Background

FOR RESEARCH USE ONLY

December 13, 2016