ImmunoReagents, Inc.
6003 Chapel Hill Road · Suite # 153 · Raleigh, NC 27607

Product Specifications

VWR Part Number: **IR1899**
ImmunoReagents, Inc. Part Number: GtxMu-003-J2ALP

Product: GOAT X MOUSE IGG ALP 1VL

Concentration: 1.50 mg/ml (E 1% at 280 nm = 13.0)

Amount: 0.5 mg

Conjugate: Alkaline Phosphatase

Form: Clear, colorless liquid

Purification: Affinity purified using solid phase Mouse IgG

Purity: > 90% based on SDS-PAGE Small amounts of intact IgG may be present.

Host: Goat

Immunogen: Purified Mouse IgG, whole molecule

Buffer: 30 mM Triethanolamine, pH 7.2, 5 mM Magnesium Chloride, 0.1 mM Zinc Chloride, 1 % (w/v) BSA, Protease/IgG free

Storage: 2-8 °C

Shelf Life: 1 year from date of receipt. Prepare working dilution prior to use and then discard.

Specificity: Based on IEP, this antibody reacts with: · heavy (?) chains on mouse IgG · light chains on all mouse immunoglobulins

Cross Reactivity: Based on IEP, no reactivity is observed to: · non-immunoglobulin mouse serum immunoglobulins · serum proteins from bovine, horse, human rabbit or swine

Country of Origin: Goat serum was obtained from healthy animals of US origin and under the care of a registered veterinarian.

Applications: This conjugate is suitable for immunomicroscopy and flow cytometry. The optimal working dilution should be determined by the investigator. Suggested starting dilution(?): · 1:20 - 1:2,000 for most applications

Disclaimer: For in vitro Laboratory Use Only. Not for diagnostic or therapeutic use. Not for human or animal consumption. Suggested applications of our products are not recommendations to use our products in violation of any patent or as a license under any patent of ImmunoReagents, Inc.

Product may not be resold or modified for resale without prior written approval of ImmunoReagents, Inc.