
Product Specifications

VWR Part Number:	IR1902
ImmunoReagents, Inc. Part Number:	GtxMu-003-LALP
Product:	GOAT X MOUSE IGG ALP 1VL
Concentration:	1.5 mg/ml (E 1% at 280 nm = 13.0)
Amount:	0.5 mg
Conjugate:	Alkaline Phosphatase
Form:	Clear, colorless liquid
Purification:	Affinity purified using solid phase Mouse IgG
Purity:	> 90% based on SDS-PAGE Small amounts of intact IgG may be present.
Host:	Goat
Immunogen:	Purified Mouse IgG, whole molecule
Buffer:	30 mM Triethanolamine, pH 7.2, 5 mM Magnesium Chloride, 0.1 mM Zinc Chloride, 1 % (w/v) BSA, Protease/IgG free
Storage:	2-8 °C
Shelf Life:	1 year from date of receipt. Prepare working dilution prior to use and then discard.
Specificity:	Based on IEP, this antibody reacts with: · heavy (?) chains on mouse IgG · light chains on all mouse immunoglobulins
Cross Reactivity:	Based on IEP, no reactivity is observed to: · non-immunoglobulin human serum immunoglobulins · bovine, goat, human, rabbit or rat IgG
Country of Origin:	Goat serum was obtained from healthy animals of US origin and under the care of a registered veterinarian.
Applications:	This conjugate is suitable for immunomicroscopy and flow cytometry. The optimal working dilution should be determined by the investigator. Suggested starting dilution(?): · 1:20 - 1:2,000 for most applications
Disclaimer:	For in vitro Laboratory Use Only. Not for diagnostic or therapeutic use. Not for human or animal consumption. Suggested applications of our products are not recommendations to use our products in violation of any patent or as a license under any patent of ImmunoReagents, Inc.

Product may not be resold or modified for resale without prior written approval of ImmunoReagents, Inc.