



CDK5 Antibody

CATALOG NUMBER: 70-439

Specifications

SPECIES REACTIVITY:	Human, Mouse, Rat
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	ELISA, IHC-P (1:100), WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	CDK5 antibody detects endogenous levels of total CDK5 protein.
IMMUNOGEN:	Synthetic peptide from human CDK5.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CDK5, CDKN5, Cell division protein kinase 5, Crk6, Cyclin-dependent kinase 5, Protein kinase CDK5 splicing, PSSALRE, TPKII catalytic subunit
ACCESSION NO.:	Q00535
PROTEIN GI NO.:	4033704
OFFICIAL SYMBOL:	CDK5
GENE ID:	1020

Background

FOR RESEARCH USE ONLY

December 13, 2016