



IL2RB / CD122 Antibody

CATALOG NUMBER: 70-441

Specifications

SPECIES REACTIVITY:	Human, Mouse, Rat
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	ELISA, IHC-P (1:66), WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	IL-2R beta/CD122 antibody detects endogenous levels of total IL-2R beta/CD122 protein.
IMMUNOGEN:	Synthetic peptide from human IL-2R beta/CD122.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	IL2RB, CD122, CD122 antigen, IL-2 receptor subunit beta, IL15RB, Interleukin 15 receptor, beta, p70-75, IL-2R subunit beta, IL-2RB, Interleukin 2 receptor, beta
ACCESSION NO.:	P14784
PROTEIN GI NO.:	124321
OFFICIAL SYMBOL:	IL2RB
GENE ID:	3560

Background

FOR RESEARCH USE ONLY

December 13, 2016