




TNFRSF8 Antibody [MEM-268]

CATALOG NUMBER: 49-104



Immunohistochemistry staining of TNFRSF8 in thymus tissue using TNFRSF8 monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	FACS, IHC
APPLICATIONS:	FACS, IHC-P (5 ug/ml)
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	TNFRSF8 monoclonal antibody was raised against an xpression vector containing CD30 cDNA booster suspension (Human).
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, 15 mM sodium azide, approx., pH 7.4.
STORAGE CONDITIONS:	TNFRSF8 antibody can be stored short term 4 °C. For long term storage aliquot and store at -20 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	TNFRSF8, CD30L receptor, CD30, Cytokine receptor CD30, D1S166E, Ki-1, Ki-1 antigen, CD30 antigen
ACCESSION NO.:	P28908
PROTEIN GI NO.:	115978
OFFICIAL SYMBOL:	TNFRSF8
GENE ID:	943

Background

BACKGROUND:

Recongizes extracellular part of CD30 (Ki-1 antigen), a 105 kDa single chain glycoprotein expressed on Hodgkin's and Reed-Sternberg cells; it is also found in Burkitt's lymphomas, virus-infected T and B lymphocytes, and on normal B and T lymphocytes after activation (T lymphocytes that produce Th2-type cytokines and on CD4+/CD8+ T lymphocytes that co-express CD45RO and the IL4 receptor).

FOR RESEARCH USE ONLY

December 13, 2016