
Product Specifications

VWR Part Number:	IR2150
ImmunoReagents, Inc. Part Number:	GtxRb-003-D350NHSX
Product:	GOAT X RABBIT IGG DYLGHT 350 1VL
Concentration:	1.0 mg/ml (E 1% at 280 nm = 13.0)
Amount:	1.0 mg
Conjugate:	DyLight® 350 (Ex = 353 nm; Em = 432 nm)
Form:	Lyophilized
Purification:	Affinity purified using solid phase Rabbit IgG
Purity:	Affinity purified antibody is > 95% based on SDS-PAGE
Host:	Goat
Immunogen:	Purified Rabbit IgG, whole molecule
Buffer:	10 mM Sodium Phosphate, 0.15 M Sodium Chloride, pH 7.2, 1 % (w/v) BSA, Protease/IgG free
Storage:	Store freeze-dried powder at 2-8 °C.
Shelf Life:	Product is stable for up to 4 weeks at 2-8°C after rehydration. For extended storage after rehydration, add an equal volume of glycerol and store at -20°C.
Specificity:	Based on IEP, this antibody reacts with: · heavy (?) chains on rabbit IgG · light chains on all rabbit immunoglobulins
Cross Reactivity:	Based on IEP, no reactivity is observed to: · non-immunoglobulin rabbit serum proteins
Country of Origin:	Goat serum was obtained from healthy animals of US origin and under the care of a registered veterinarian.
Applications:	This conjugate is suitable for immunomicroscopy and flow cytometry. The optimal working dilution should be determined by the investigator. Suggested starting dilution(?): · 1:20 - 1:2,000 for most applications
Disclaimer:	For in vitro Laboratory Use Only. Not for diagnostic or therapeutic use. Not for human or animal consumption. Suggested applications of our products are not recommendations to use our products in violation of any patent or as a license under any patent of ImmunoReagents, Inc.

Product may not be resold or modified for resale without prior written approval of ImmunoReagents, Inc.