




Vimentin Antibody [VI-10]

CATALOG NUMBER: 49-109



Immunohistochemistry staining of Vimentin in skin tissue using Vimentin monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Chicken, Human, Mouse, Pig, Rat
TESTED APPLICATIONS:	ICC, IHC, IP, WB
APPLICATIONS:	ICC, IHC-P (5 ug/ml), IP, WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Reacts with vimentin, a 57 kDa intermediate filament expressed in variety of mesenchymal and mesodermal cell types.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Caprylic acid and ammonium sulfate precipitation
PHYSICAL STATE:	Liquid
BUFFER:	PBS, 15 mM sodium azide, approx., pH 7.4.
STORAGE CONDITIONS:	Store Vimentin antibody at 4 °C, Avoid Freezing
CLONALITY:	Monoclonal
ISOTYPE:	IgM
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	VIM, Vimentin
ACCESSION NO.:	P08670
PROTEIN GI NO.:	55977767
OFFICIAL SYMBOL:	VIM
GENE ID:	7431

Background

