




HDAC3 Antibody [7G6C5]

CATALOG NUMBER: 51-316



Immunohistochemistry of human
cerebellum tissue stained using HDAC3
Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IF, IHC, WB
APPLICATIONS:	HDAC3 antibody can be used in ELISA starting at 1:000 - 1:1000, and immunohistochemistry starting at 10 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant protein encoding amino acids 224 to 428 of human HDAC3.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Ascites
PHYSICAL STATE:	Liquid
BUFFER:	0.03% sodium azide
STORAGE CONDITIONS:	HDAC3 antibody should be stored long term (months) at -20 °C and short term (weeks) at 4 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	HDAC3, RPD3, SMAP45, HD3, Histone deacetylase 3, RPD3-2
ACCESSION NO.:	O15379
PROTEIN GI NO.:	3334210
OFFICIAL SYMBOL:	HDAC3
GENE ID:	8841

Background

