




## GOT2 Antibody [3E9]

CATALOG NUMBER: 51-328



Immunohistochemistry of Human brain  
cortex tissue stained using GOT2  
Monoclonal Antibody.

### Specifications

<b>SPECIES REACTIVITY:</b>	Rat
<b>TESTED APPLICATIONS:</b>	IF
<b>APPLICATIONS:</b>	GOT2 antibody can be used in ELISA starting at 1:30000 - 1:160000, Western Blot starting at 1:500 - 1:3000, and immunohistochemistry starting at 2.5 ug/mL.
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>IMMUNOGEN:</b>	Purified recombinant fragment of human GOT2 expressed in E. Coli.
<b>HOST SPECIES:</b>	Mouse

### Properties

<b>PURIFICATION:</b>	Ascites
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	0.03% sodium azide
<b>STORAGE CONDITIONS:</b>	GOT2 antibody should be stored long term (months) at -20 °C and short term (weeks) at 4 °C. As with all antibodies avoid freeze/thaw cycles.
<b>CLONALITY:</b>	Monoclonal
<b>ISOTYPE:</b>	IgG1
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	GOT2, FABP-1, MitAAT, Transaminase A, FABPpm, Fatty acid-binding protein, KAT4, KATIV, Kynurenine aminotransferase IV, MAspAT
<b>ACCESSION NO.:</b>	P00505
<b>PROTEIN GI NO.:</b>	308153643
<b>OFFICIAL SYMBOL:</b>	GOT2
<b>GENE ID:</b>	2806

