




FGR Antibody [6G2]

CATALOG NUMBER: 51-374



Immunohistochemistry of human spleen tissue stained using FGR Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human, Mouse
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	FGR antibody can be used in ELISA starting at 1:000 - 1:1000, and immunohistochemistry starting at 5 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant protein
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Ascites
PHYSICAL STATE:	Liquid
BUFFER:	0.03% sodium azide
STORAGE CONDITIONS:	FGR antibody should be stored long term (months) at -20 °C and short term (weeks) at 4 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	FGR, C-fgr protooncogene, C-src2, C-fgr, Fgr kinase, Fgr oncogene, p55-Fgr, p58-Fgr, p58c-fgr, Proto-oncogene c-Fgr, Tyrosine-protein kinase Fgr, p55c-fgr, SRC2, C-src-2 proto-oncogene, Fgr proto oncogene, p55-c-fgr protein
ACCESSION NO.:	P09769
PROTEIN GI NO.:	125358
OFFICIAL SYMBOL:	FGR
GENE ID:	2268

FOR RESEARCH USE ONLY

December 13, 2016