




DUT Antibody [1C9]

CATALOG NUMBER: 51-452



Immunohistochemistry of human tonsil tissue stained using DUT Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IF, IHC, WB
APPLICATIONS:	DUT antibody can be used in immunohistochemistry starting at 5 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	DUT (AAH33645, 68 a.a. ~ 164 a.a) partial recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	Store DUT antibody at -20 °C. Aliquot to avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	DUT, Deoxyuridine triphosphatase, DUTP pyrophosphatase, DUT-N, DUTP nucleotidohydrolase, DUTPase
ACCESSION NO.:	P33316
PROTEIN GI NO.:	347595814
OFFICIAL SYMBOL:	DUT
GENE ID:	1854

Background

