




USP33 Antibody [5B5]

CATALOG NUMBER: 51-745



Immunohistochemistry of human tonsil tissue stained using USP33 Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IF, IHC, IP, WB
APPLICATIONS:	USP33 antibody can be used in ELISA starting at 1 ug/mL, Western Blot starting at 1 ug/mL, and immunohistochemistry starting at 20 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant protein
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	USP33 antibody can be stored short term 4 °C. For long term storage aliquot and store at -20 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	USP33, Deubiquitinating enzyme 33, KIAA1097, HVDU1, VDU1, Ubiquitin thioesterase 33, Ubiquitin thiolesterase 33, Ubiquitin specific protease 33
ACCESSION NO.:	Q8TEY7
PROTEIN GI NO.:	116242838
OFFICIAL SYMBOL:	USP33
GENE ID:	23032

