




RARA Antibody [2D2]

CATALOG NUMBER: 51-794



Immunohistochemistry of human testis tissue stained using RARA Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	RARA antibody can be used in ELISA, immunohistochemistry starting at 10 ug/mL, and immunocytochemistry.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant protein
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	RARA antibody can be stored short term 4 °C. For long term storage aliquot and store at -20 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	RARA, NR1B1, PML-RAR, RAR-alpha, RARalpha, Retinoic acid receptor alpha, Pml-rara, RAR, RAR alpha, Retinoic acid receptor, alpha
ACCESSION NO.:	P10276
PROTEIN GI NO.:	133483
OFFICIAL SYMBOL:	RARA
GENE ID:	5914

Background

