




## HADH Antibody [4B5]

CATALOG NUMBER: 51-955



Immunohistochemistry of human heart tissue stained using HADH Monoclonal Antibody.

### Specifications

<b>SPECIES REACTIVITY:</b>	Human
<b>TESTED APPLICATIONS:</b>	ELISA, IF, IHC, IP, WB
<b>APPLICATIONS:</b>	HADH antibody can be used in ELISA starting at 1:000 - 1:1000, and immunohistochemistry starting at 20 ug/mL.
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>IMMUNOGEN:</b>	HADHSC (NP_005318, 205 a.a. ~ 315 a.a) partial recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
<b>HOST SPECIES:</b>	Mouse

### Properties

<b>PURIFICATION:</b>	Protein A Column
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	PBS, pH 7.2
<b>STORAGE CONDITIONS:</b>	Aliquot and store HADH antibody at -20 °C or -80 °C. As with all antibodies avoid freeze/thaw cycles.
<b>CLONALITY:</b>	Monoclonal
<b>ISOTYPE:</b>	IgG2b,k
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	HADH, HAD, HADH1, HCDH, HHF4, SCHAD, HADHSC, Hydroxyacyl-CoA dehydrogenase, MSCHAD
<b>ACCESSION NO.:</b>	Q16836
<b>PROTEIN GI NO.:</b>	311033442
<b>OFFICIAL SYMBOL:</b>	HADH
<b>GENE ID:</b>	3033

### Background

