



Factor 9 Antibody

CATALOG NUMBER: 70-269

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC
APPLICATIONS:	Factor 9 Antibody can be used for immunohistochemistry (tested on parafin embedded tissues) starting at 5 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Recognizes human Factor IX as demonstrated by immunodiffusion. A single positive reactivity band was observed with Normal Human Plasma. No reaction was observed against F. IX-deficient plasma.
IMMUNOGEN:	Human Factor IX (F. IX) purified from plasma.
HOST SPECIES:	Sheep

Properties

PURIFICATION:	Ammonium Sulfate Precipitation
PHYSICAL STATE:	Liquid
BUFFER:	0.01 M HEPES, pH 7.4, 0.1 M sodium chloride, 50% glycerol.
STORAGE CONDITIONS:	Factor 9 antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	F9, Christmas Disease, Coagulation factor IX, Factor IX Deficiency, FIX, HEMB, F9 p22, Factor 9, Factor IX, Factor IX F9, FIX F9, Haemophilia B, THPH8, Christmas factor, Hemophilia B, PTC, Serine protease
ACCESSION NO.:	P00740
PROTEIN GI NO.:	67476446
OFFICIAL SYMBOL:	F9
GENE ID:	2158

Background

FOR RESEARCH USE ONLY

December 13, 2016