



## GLI1 Antibody

CATALOG NUMBER: 70-343

### Specifications

|                             |   |
|-----------------------------|---|
| <b>SPECIES REACTIVITY:</b>  | Human, Monkey   |
| <b>TESTED APPLICATIONS:</b> | IHC, WB   |
| <b>APPLICATIONS:</b>        | GLI1 Antibody can be used for Immunohistochemistry in paraffin embedded tissues starting at 5 - 10 ug/mL, and Western Blotting starting at 1 - 3 ug/mL. |
| <b>USER NOTE:</b>           | Optimal dilutions for each application to be determined by the researcher.  |
| <b>IMMUNOGEN:</b>           | A portion of amino acids 940-990 of human GLI1 was used as the immunogen.   |
| <b>HOST SPECIES:</b>        | Rabbit  |

### Properties

|                            |   |
|----------------------------|---|
| <b>PURIFICATION:</b>       | Protein A Column  |
| <b>BUFFER:</b>             | PBS, 0.2% gelatin, 0.05% sodium azide   |
| <b>CONCENTRATION:</b>      | 0.5 mg/ml   |
| <b>STORAGE CONDITIONS:</b> | Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles. |
| <b>CLONALITY:</b>          | Polyclonal  |
| <b>CONJUGATE:</b>          | Unconjugated  |

### Additional Info

|                         |  |
|-------------------------|--|
| <b>ALTERNATE NAMES:</b> | GLI1, Gli-1, GLI family zinc finger 1, Glioma-associated oncogene, Glioma-associated oncogene 1, Oncogene GLI, GLI, Zinc finger protein GLI1 |
| <b>ACCESSION NO.:</b>   | P08151   |
| <b>PROTEIN GI NO.:</b>  | 121323   |
| <b>OFFICIAL SYMBOL:</b> | GLI1   |
| <b>GENE ID:</b>         | 2735   |

### Background

FOR RESEARCH USE ONLY

December 13, 2016