



## TNK2 / ACK1 Antibody

CATALOG NUMBER: 70-617

### Specifications

<b>SPECIES REACTIVITY:</b>	Human, Mouse, Rat
<b>TESTED APPLICATIONS:</b>	ELISA, IHC, WB
<b>APPLICATIONS:</b>	TNK2 / ACK1 Antibody can be used for ELISA starting at 1:16000, and Immunohistochemistry in paraffin embedded tissues starting at 1.25 ug/mL,
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>IMMUNOGEN:</b>	Synthetic peptide
<b>HOST SPECIES:</b>	Rabbit

### Properties

<b>PURIFICATION:</b>	Purified
<b>BUFFER:</b>	PBS, pH 7.4, 0.05% sodium azide
<b>CONCENTRATION:</b>	1 mg/ml
<b>STORAGE CONDITIONS:</b>	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
<b>CLONALITY:</b>	Polyclonal
<b>ISOTYPE:</b>	IgG
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	TNK2, ACK, Activated p21cdc42Hs kinase, Ack kinase, ACK-1, ACK1, Activated CDC42 kinase 1, p21cdc42Hs
<b>ACCESSION NO.:</b>	Q07912
<b>PROTEIN GI NO.:</b>	229462980
<b>OFFICIAL SYMBOL:</b>	TNK2
<b>GENE ID:</b>	10188

### Background

FOR RESEARCH USE ONLY

December 13, 2016