




Nicastrin Antibody [AT3B2]

CATALOG NUMBER: 49-072



Human brain cortex tissue stained with
Antibody, alkaline phosphatase-
streptavidin and chromogen.

Specifications

SPECIES REACTIVITY:	Human, Mouse
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	Nicastrin antibody can be used in ELISA, Western Blot, and immunohistochemistry starting at 5 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant human Nicastrin (34-153aa) purified from E. coli
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein G Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.4, 0.1% sodium azide
STORAGE CONDITIONS:	Aliquot and store Nicastrin antibody at -20 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2b,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	NCSTN, Anterior pharynx-defective 2, ATAG1874, KIAA0253, Nicastrin, APH2, RP11-517F10.1
ACCESSION NO.:	Q92542
PROTEIN GI NO.:	12231037
OFFICIAL SYMBOL:	NCSTN
GENE ID:	23385

Background

FOR RESEARCH USE ONLY

