




## NCAM1 Antibody [MEM-188]

CATALOG NUMBER: 49-121



Immunohistochemistry staining of NCAM1  
in brain cortex tissue using NCAM1  
monoclonal Antibody.

### Specifications

<b>SPECIES REACTIVITY:</b>	Bovine, Human, Pig
<b>TESTED APPLICATIONS:</b>	FACS, IHC, IP, WB
<b>APPLICATIONS:</b>	NCAM1 antibody can be used in immunohistochemistry starting at 5 ug/mL.
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>IMMUNOGEN:</b>	NCAM1 monoclonal antibody was raised against KG - 1 human acute myeloid leukemia cell line (Human).
<b>HOST SPECIES:</b>	Mouse

### Properties

<b>PURIFICATION:</b>	Affinity Chromatography
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	Phosphate-buffered solution, pH 7.2, 0.09% sodium azide.
<b>STORAGE CONDITIONS:</b>	Store NCAM1 antibody at 4 °C.
<b>CLONALITY:</b>	Monoclonal
<b>ISOTYPE:</b>	IgG2a
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	NCAM1, CD56, CD56 antigen, MSK39, NCAM-1, N-CAM-1, NCAM
<b>ACCESSION NO.:</b>	P13591
<b>PROTEIN GI NO.:</b>	205830665
<b>OFFICIAL SYMBOL:</b>	NCAM1
<b>GENE ID:</b>	4684

### Background

FOR RESEARCH USE ONLY

