

SAFETY DATA SHEET

Prolex[™] Staph Latex Kit

Section 1. Identification

GHS product identifier	: Prolex [™] Staph Latex Kit
Other means of identification	: Not available.
Trade name	: Prolex [™] Staph Latex Kit : Staph Test Latex Reagent Negative Control Latex Reagent Staph Positive Control Reagent

Code

PL.080B; PL.081B PL.083B; PL.084B PL.085B; PL.086B PL.089B

Identified uses

The Prolex[™] Staph Latex Kit provides a rapid platform for the identification of Staphylococcal isolates particularly *Staphylococcus aureus* which possess bound coagulase (clumping factor) and / or protein A from other species of staphylococci.

Supplier's details	: Pro-Lab Diagnostics 20 Mural Street, Unit 4 Richmond Hill, ON Canada L4B 1K3 Tel: +1-905-731-0300 Fax: +1-905-731-0206 www.pro-lab.com
Emergency telephone	: 905-731-0300 –Monday to Friday 8:30 am to 5:00 pm Eastern Standard Time.
number (with hours of	416-230-0692 –Outside the above hours.

operation)

Section 2. Hazards identification

OSHA/HCS status	While this material is not considered hazardous by the OSHA Hazard Communicatio Standard (29 CFR 1910.1200), this SDS contains valuable information critical to the safe handling and proper use of the product. This SDS should be retained and availar for employees and other users of this product.	
Classification of the	PL.083B, PL.084B Not classified.	
substance or mixture	PL.089B Not classified.	
	PL.085B, PL.086B Not classified.	
GHS label elements		
Signal word	No signal word.	
Hazard statements	No known significant effects or critical hazards.	
Precautionary statements		
Prevention	Not applicable.	
Response	Not applicable.	
Storage	Not applicable.	
Disposal	Not applicable.	
Hazards not otherwise class	<u>d (HNOC)</u>	

Tel: +1-888-GHS-7769 (447-7769) / +1-450-GHS-7767 (447-7767) www.kmkregservices.com www.askdrluc.com www.ghssmart.com



Section 2. Hazards identification

Physical hazards not otherwise classified (PHNOC)	:	None known.
Health hazards not otherwise classified (HHNOC)	:	None known.

Section 3. Composition/information on ingredients

Substance/mixture	: Mixture
Other means of	: Not available.
identification	

CAS number/other identifiers

CAS number

: Not applicable.

Ingredient name	%	CAS number
Staph Test Latex Reagent Boric acid	0.1 - 1	10043-35-3

Any concentration shown as a range is to protect confidentiality or is due to batch variation.

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

Occupational exposure limits, if available, are listed in Section 8.

Section 4. First aid measures

Description of necessary first aid measures

Eye contact	 Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Get medical attention if irritation occurs.
Inhalation	: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical attention if symptoms occur.
Skin contact	: Flush contaminated skin with plenty of water. Get medical attention if symptoms occur.
Ingestion	: Wash out mouth with water. Get medical attention if symptoms occur.

Most important symptoms/effects, acute and delayed

Potential acute health effects

Eye contact	: PL.083B, PL.084B PL.089B PL.085B, PL.086B	No known significant effects or critical hazards. No known significant effects or critical hazards. No known significant effects or critical hazards.
Inhalation	: PL.083B, PL.084B PL.089B PL.085B, PL.086B	No known significant effects or critical hazards. No known significant effects or critical hazards. No known significant effects or critical hazards.
Skin contact	: PL.083B, PL.084B PL.089B PL.085B, PL.086B	No known significant effects or critical hazards. No known significant effects or critical hazards. No known significant effects or critical hazards.
Ingestion	: PL.083B, PL.084B PL.089B PL.085B, PL.086B	No known significant effects or critical hazards. No known significant effects or critical hazards. No known significant effects or critical hazards.

Over-exposure signs/symptoms

: No known significant effects or critical hazards.

Eye contact

Tel : +1-888-GHS-7769 (447-7769) / +1-450-GHS-7767 (447-7767) www.kmkregservices.com www.askdrluc.com www.ghssmart.com



Section 4. First aid measures

Inhalation	: No known significant effects or critical hazards.
Skin contact	: No known significant effects or critical hazards.
Ingestion	: No known significant effects or critical hazards.

Indication of immediate medical attention and special treatment needed, if necessary

Notes to physician	 Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.
Specific treatments	: No specific treatment.
Protection of first-aiders	: No action shall be taken involving any personal risk or without suitable training.

See toxicological information (Section 11)

Section 5. Fire-fighting measures

Extinguishing media	
Suitable extinguishing media	: Use an extinguishing agent suitable for the surrounding fire.
Unsuitable extinguishing media	: None known.
Specific hazards arising from the chemical	: No specific fire or explosion hazard.
Hazardous thermal decomposition products	: No specific data.
Special protective actions for fire-fighters	: No special measures are required.
Special protective equipment for fire-fighters	: Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

Section 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

For non-emergency personnel	:	Put on appropriate personal protective equipment.
For emergency responders	:	If specialized clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".
Environmental precautions Methods and materials for con		Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).
Spill		Stop leak if without risk. Move containers from spill area. Prevent entry into sewers,
- - - - - - - - - -		water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see Section 13). Dispose of via a licensed waste disposal contractor. Note: see Section 1 for emergency contact information and Section 13 for waste disposal.



Section 7. Handling and storage

Precautions for safe handling	L	
Protective measures	:	Put on appropriate personal protective equipment (see Section 8).
Advice on general occupational hygiene	:	Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. See also Section 8 for additional information on hygiene measures.
Conditions for safe storage, including any incompatibilities	:	Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabeled containers. Use appropriate containment to avoid environmental contamination. Store at 2°C to 8°C.

Section 8. Exposure controls/personal protection

Control parameters

Occupational exposure limits

Ingredient name	Exposure limits
Staph Test Latex Reagent Boric acid	ACGIH TLV (United States, 4/2014). STEL: 6 mg/m ³ 15 minutes. Form: Inhalable fraction TWA: 2 mg/m ³ 8 hours. Form: Inhalable fraction

Canada

Occupational exposure limits		TWA (8 hours)		STEL (15 mins)		Ceiling					
Ingredient	List name	ppm	mg/m³	Other	ppm	mg/m³	Other	ppm	mg/m³	Other	Notations
	US ACGIH 4/2014 BC 7/2013 ON 1/2013	- -	2 2 2	- - -	- - -	6 6 6	- -		- -	-	[a] [b] [a]

Form: [a]Inhalable fraction [b]Inhalable

Appropriate engineering controls	:	Good general ventilation should be sufficient to control worker exposure to airborne contaminants.
Environmental exposure controls	:	Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation.
Individual protection measure	<u>es</u>	
Hygiene measures	:	Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Ensure that eyewash stations and safety showers are close to the workstation location.
Eye/face protection	:	Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts.
Skin protection		
Hand protection	:	Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.



Section 8. Exposure controls/personal protection

Body protection	: Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
Other skin protection	 Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
Respiratory protection	: Not required under normal conditions of use.

Section 9. Physical and chemical properties

Appearance

Physical state	-	PL.083B, PL.084B PL.085B, PL.086B PL.089B	Liquid. [Suspension.] Liquid. [Suspension.] Liquid. [Solution.]
Color	:	PL.083B, PL.084B PL.085B, PL.086B PL.089B	Blue. Blue. Colorless.
Odor	:	Not available.	
Odor threshold	:	Not available.	
рН	-	PL.083B, PL.084B PL.085B, PL.086B PL.089B	8 8 6
Melting point	1		
Boiling point	1	Not available.	
Flash point	1	Not available.	
Evaporation rate	1	Not available.	
Flammability (solid, gas)	1	Not available.	
Lower and upper explosive (flammable) limits	1	Not available.	
Vapor pressure	1	Not available.	
Vapor density	1	Not available.	
Relative density	1	Not available.	
Solubility	:	PL.083B, PL.084B PL.089B PL.085B, PL.086B	Not available. Not available. Not available.
Partition coefficient: n- octanol/water	:	Not available.	
Auto-ignition temperature	:	Not available.	
Decomposition temperature	:	Not available.	
Viscosity	1	Not available.	
Volatility	1	Not available.	

Section 10. Stability and reactivity

Reactivity	: No specific test data related to reactivity available for this product or its ingredients.	
Chemical stability	: The product is stable.	
Possibility of hazardous reactions	: Under normal conditions of storage and use, hazardous reactions will not occur.	
	Tel : +1-888-GHS-7769 (447-7769) / +1-450-GHS-7767 (447-7767)	

Kĸ

Tel : +1-888-GHS-7769 (447-7769) / +1-450-GHS-7767 (447-7767) www.kmkregservices.com www.askdrluc.com www.ghssmart.com



Section 10. Stability and reactivity

Section 11 Toxic	logical information	
Hazardous decomposition products	: Under normal conditions of storage and use, hazardous decomposition products should not be produced.	
Incompatible materials	: Reactive or incompatible with the following materials: oxidizing materials.	
Conditions to avoid	: No specific data.	

Section 11. Toxicological information

Information on toxicological effects

Acute toxicity

There is no data available.

Irritation/Corrosion

Product/ingredient name	Result	Species	Score	Exposure	Observation
Staph Test Latex Reagent Boric acid	Skin - Mild irritant	Human	-	72 hours 15 mg Intermittent	-

Sensitization

There is no data available.

Carcinogenicity

There is no data available.

Specific target organ toxicity (single exposure)

There is no data available.

Specific target organ toxicity (repeated exposure)

There is no data available.

Aspiration hazard

There is no data available.

Information on the likely : Dermal contact. Eye contact. Inhalation. Ingestion.

routes of exposure

Potential acute health effects

Eye contact	: PL.083B, PL.084B PL.089B PL.085B, PL.086B	No known significant effects or critical hazards. No known significant effects or critical hazards. No known significant effects or critical hazards.
Inhalation	: PL.083B, PL.084B PL.089B PL.085B, PL.086B	No known significant effects or critical hazards. No known significant effects or critical hazards. No known significant effects or critical hazards.
Skin contact	: PL.083B, PL.084B PL.089B PL.085B, PL.086B	No known significant effects or critical hazards. No known significant effects or critical hazards. No known significant effects or critical hazards.
Ingestion	: PL.083B, PL.084B PL.089B PL.085B, PL.086B	No known significant effects or critical hazards. No known significant effects or critical hazards. No known significant effects or critical hazards.

Symptoms related to the physical, chemical and toxicological characteristics

Eye contact
Inhalation

: No known significant effects or critical hazards.

: No known significant effects or critical hazards.

ODDDD PRO-LAB

Section 11. Toxicological information

Skin contact	: No known significant effects or critical hazards.
Ingestion	: No known significant effects or critical hazards.

Delayed and immediate effect	ts :	and also chronic effects from short and long term exposure
<u>Short term exposure</u>		
Potential immediate effects	:	No known significant effects or critical hazards.
Potential delayed effects	1	No known significant effects or critical hazards.
Long term exposure		
Potential immediate effects	:	No known significant effects or critical hazards.
Potential delayed effects	1	No known significant effects or critical hazards.
Potential chronic health effe	ct	<u>5</u>
General	1	No known significant effects or critical hazards.
Carcinogenicity	1	No known significant effects or critical hazards.
Mutagenicity	1	No known significant effects or critical hazards.
Teratogenicity	1	No known significant effects or critical hazards.
Developmental effects	1	No known significant effects or critical hazards.
Fertility effects	1	No known significant effects or critical hazards.

Numerical measures of toxicity

Acute toxicity estimates

There is no data available.

Section 12. Ecological information

Toxicity

Product/ingredient name	Result	Species	Exposure	
Staph Test Latex Reagent				
Boric acid	Acute LC50 84.28 mg/L Marine water	Crustaceans - Americamysis bahia - Juvenile (Fledgling, Hatchling, Weanling)	48 hours	
	Acute LC50 133000 µg/L Fresh water	Daphnia - Daphnia magna - Neonate	48 hours	
	Acute LC50 100000 µg/L Fresh water	Fish - Ptychocheilus lucius - Juvenile (Fledgling, Hatchling, Weanling)	96 hours	
	Chronic NOEC 6000 μ g/L Fresh water Chronic NOEC 2100 μ g/L Fresh water	Daphnia - Daphnia magna Fish - Oncorhynchus mykiss	21 days 87 days	

Persistence and degradability

There is no data available.

Bioaccumulative potential

Product/ingredient name	LogPow	BCF	Potential
Staph Test Latex Reagent Boric acid	-1.09	-	low

Mobility in soil

Soil/water partition coefficient (K _{oc})	
Mobility	

No data available.No data available.





Section 12. Ecological information

Other adverse effects

: No known significant effects or critical hazards.

Section 13. Disposal considerations

Disposal methods : The generation of waste should be avoided or minimized wherever possible. Disposal of this product, solutions and any by-products should comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

Section 14. Transport information

	DOT	TDG	IMDG	ΙΑΤΑ
UN number	Not regulated.	Not regulated.	Not regulated.	Not regulated.
UN proper shipping name	-	-		-
Transport hazard class(es)	-	-	-	-
Packing group	-	-		-
Environmental hazards	No.	No.	No.	No.
Additional information	-	-		-

AERG : Not applicable.

Special precautions for user : Transport within user's premises: always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

Transport in bulk according : Not available. to Annex II of MARPOL 73/78 and the IBC Code

Section 15. Regulatory information

U.S. Federal regulations : TSCA 4(a) proposed test rules: Glycine TSCA 8(a) CDR Exempt/Partial exemption: Not determined United States inventory (TSCA 8b): All components are listed or exempted. Clean Water Act (CWA) 311: Acetic acid



Section 15. Regulatory information

Clean Air Act Section 112 (b) Hazardous Air Pollutants (HAPs)	: Not listed
Clean Air Act Section 602 Class I Substances	: Not listed
Clean Air Act Section 602 Class II Substances	: Not listed
DEA List I Chemicals (Precursor Chemicals)	: Not listed
DEA List II Chemicals (Essential Chemicals)	: Not listed

SARA 302/304

Composition/information on ingredients

			SARA 302 TPQ		SARA 304 RQ	
Name	%	EHS	(lbs)	(gallons)	(lbs)	(gallons)
Staph Test Latex Reagent Sodium azide Staph Positive Control Reagent	0.025 - 0.1	Yes.	500	-	1000	-
Sodium azide Negative Control Latex Reagent	0 - 0.01	Yes.	500	-	1000	-
Sodium azide	0.025 - 0.1	Yes.	500	-	1000	-

SARA 304 RQ

: 1048359.8 lbs / 475955.4 kg

SARA 311/312

Classification

: Not applicable.

Composition/information on ingredients

Name	%	hazard	Sudden release of pressure		(acute) health	Delayed (chronic) health hazard
Staph Test Latex Reagent Boric acid	0.1 - 1	No.	No.	No.	No.	Yes.

State regulations

Massachusetts

New York

: None of the components are listed.

: None of the components are listed.

- **New Jersey**
 - : None of the components are listed. : None of the components are listed.
- **Pennsylvania** California Prop. 65

No products were found.

- Canada
- **Canadian lists**
- **Canadian NPRI**
- : None of the components are listed.
- **CEPA Toxic substances** : None of the components are listed.
- **Canada inventory**
- : All components are listed or exempted.



Section 16. Other information

<u>History</u>		
Date of issue mm/dd/yyyy	1	05/15/2015
Date of previous issue	:	10/15/2012
Version	:	3
Prepared by	:	KMK Regulatory Services Inc.
Key to abbreviations	:	ATE = Acute Toxicity Estimate BCF = Bioconcentration Factor GHS = Globally Harmonized System of Classification and Labelling of Chemicals IATA = International Air Transport Association IBC = Internediate Bulk Container IMDG = International Maritime Dangerous Goods LogPow = logarithm of the octanol/water partition coefficient MARPOL 73/78 = International Convention for the Prevention of Pollution From Ships, 1973 as modified by the Protocol of 1978. ("Marpol" = marine pollution) UN = United Nations

Notice to reader

.

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.

