




Prohibitin 2 Antibody

CATALOG NUMBER: 49-128



Immunohistochemistry staining of
Prohibitin 2 in brain cortex tissue using
Prohibitin 2 Antibody.

Specifications

SPECIES REACTIVITY:	Human, Mouse
TESTED APPLICATIONS:	ICC, IHC, WB
APPLICATIONS:	Prohibitin 2 antibody can be used in ELISA, and immunohistochemistry starting at 10 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Prohibitin 2 antibody was raised against recombinant (partial), C-Terminal region of Prohibitin 2 (Mouse).
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
PHYSICAL STATE:	Liquid
BUFFER:	Phosphate-buffered solution, pH 7.2, 0.09% sodium azide, 50% glycerol.
STORAGE CONDITIONS:	Store Prohibitin 2 antibody at -20 °C. Aliquot to avoid freeze/thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	PHB2, BCAP37, BAP, D-prohibitin, p22, Prohibitin-2, B-cell associated protein, Bap37, PNAS-141, Prohibitin 2, REA
ACCESSION NO.:	Q99623
PROTEIN GI NO.:	74752151
OFFICIAL SYMBOL:	PHB2
GENE ID:	11331

Background

