




Basigin Antibody [HIM6]

CATALOG NUMBER: 49-195



Immunohistochemistry staining of Basigin
in testis tissue using Basigin monoclonal
Antibody.

Specifications

| | |
|-----------------------------|--|
| SPECIES REACTIVITY: | Human |
| TESTED APPLICATIONS: | FACS, IHC, WB |
| APPLICATIONS: | Basigin antibody can be used in immunohistochemistry starting at 10 ug/mL, and immunohistochemistry in frozen tissues starting at 1:400 - 1:600. |
| USER NOTE: | Optimal dilutions for each application to be determined by the researcher. |
| HOST SPECIES: | Mouse |

Properties

| | |
|----------------------------|---|
| PURIFICATION: | Affinity Chromatography |
| PHYSICAL STATE: | Liquid |
| BUFFER: | PBS, pH 7.2, 0.09% sodium azide. |
| STORAGE CONDITIONS: | Store Basigin antibody undiluted at 4 °C. |
| CLONALITY: | Monoclonal |
| ISOTYPE: | IgG1 |
| CONJUGATE: | Unconjugated |

Additional Info

| | |
|-------------------------|--|
| ALTERNATE NAMES: | BSG, 5F7, Basigin, Basigin (Ok blood group), CD147 antigen, Collagenase stimulatory factor, EMMPRIN, OK, OK blood group antigen, TCSF, CD147, M6 |
| ACCESSION NO.: | P35613 |
| PROTEIN GI NO.: | 51704273 |
| OFFICIAL SYMBOL: | BSG |
| GENE ID: | 682 |

Background

FOR RESEARCH USE ONLY

