




## CD177 Antibody [MEM-166]

CATALOG NUMBER: 49-198



Immunohistochemistry staining of CD177  
in intravascular neutrophils tissue using  
CD177 monoclonal Antibody.

### Specifications

<b>SPECIES REACTIVITY:</b>	Human, Monkey
<b>TESTED APPLICATIONS:</b>	FACS, IHC, IP, WB
<b>APPLICATIONS:</b>	CD177 antibody can be used in immunohistochemistry starting at 10 ug/mL.
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>SPECIFICITY:</b>	Human granulocytes
<b>IMMUNOGEN:</b>	CD177 monoclonal antibody was raised against full length CD177 (Human).
<b>HOST SPECIES:</b>	Mouse

### Properties

<b>PURIFICATION:</b>	Affinity Chromatography
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	Phosphate-buffered solution, pH 7.2, 0.09% sodium azide.
<b>STORAGE CONDITIONS:</b>	Store CD177 antibody undiluted at 4 °C.
<b>CLONALITY:</b>	Monoclonal
<b>ISOTYPE:</b>	IgG1
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	CD177, CD177 molecule, CD177 antigen, Cell surface receptor, HNA-2a, HNA2A, NB1, PRV-1, Polycythemia rubra vera 1, PRV1, NB1 glycoprotein, NB1 GP
<b>ACCESSION NO.:</b>	Q8N6Q3
<b>PROTEIN GI NO.:</b>	91208246
<b>OFFICIAL SYMBOL:</b>	CD177
<b>GENE ID:</b>	57126

### Background

