




Caspase-12 Antibody

CATALOG NUMBER: 49-614



Immunohistochemistry staining of
Caspase-12 in brain cortex tissue using
Caspase-12 Antibody.

Specifications

SPECIES REACTIVITY:	Human, Mouse, Rat
TESTED APPLICATIONS:	IHC, WB
APPLICATIONS:	Caspase-12 antibody can be used in ELISA, Western Blot, and immunohistochemistry starting at 10 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Caspase-12 antibody was raised against amino acids 2 - 17 of Caspase-12 (Human).
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
PHYSICAL STATE:	Liquid
BUFFER:	PBS, 0.02% sodium azide.
STORAGE CONDITIONS:	Store Caspase-12 antibody at 4 °C or -20 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CASP12, Caspase 12 pseudogene 1, Caspase 12, CASP-12, Caspase 12 (gene/pseudogene), Inactive caspase-12, CASP12P1
ACCESSION NO.:	Q6UXS9
PROTEIN GI NO.:	395398427
OFFICIAL SYMBOL:	CASP12
GENE ID:	100506742

Background

FOR RESEARCH USE ONLY

