




Trefoil Factor 2 Antibody

CATALOG NUMBER: 49-985



Immunohistochemistry staining of Trefoil Factor 2 in placenta tissue using Trefoil Factor 2 Antibody.

Specifications

SPECIES REACTIVITY:	Gorilla, Human
TESTED APPLICATIONS:	IHC
APPLICATIONS:	Trefoil Factor 2 antibody can be used in ELISA, and immunohistochemistry starting at 10 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	BLAST analysis of the peptide immunogen showed no homology with other human proteins.
IMMUNOGEN:	Trefoil Factor 2 antibody was raised against synthetic peptide corresponding to an internal domain of human Trefoil Factor 2 (Human).
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
PHYSICAL STATE:	Liquid
BUFFER:	PBS, 0.1% sodium azide.
STORAGE CONDITIONS:	Trefoil Factor 2 antibody should be stored long term (months) at -80 °C and short term (days) at 4 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	TFF2, SP, Spasmolysin, Trefoil factor 2, SML1, Spasmolytic polypeptide, Spasmolytic protein 1
ACCESSION NO.:	Q03403
PROTEIN GI NO.:	2833194
OFFICIAL SYMBOL:	TFF2
GENE ID:	7032

Background

