




## TARDBP Antibody [2E2-D3]

CATALOG NUMBER: 51-577



Immunohistochemistry of human brain  
cortex tissue stained using TARDBP  
Monoclonal Antibody.

### Specifications

<b>SPECIES REACTIVITY:</b>	Human
<b>TESTED APPLICATIONS:</b>	ELISA, IF, IHC, RNAi, WB
<b>APPLICATIONS:</b>	TARDBP antibody can be used in ELISA, Western Blot starting at 1:500 - 1:1000, and immunohistochemistry starting at 5 ug/mL.
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>IMMUNOGEN:</b>	TARDBP (AAH01487, 1 a.a. ~ 261 a.a) full length recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
<b>HOST SPECIES:</b>	Mouse

### Properties

<b>PURIFICATION:</b>	Protein A Column
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	PBS, pH 7.2
<b>CONCENTRATION:</b>	0.47 mg/ml
<b>STORAGE CONDITIONS:</b>	Store TARDBP antibody at -20 °C. Aliquot to avoid freeze/thaw cycles.
<b>CLONALITY:</b>	Monoclonal
<b>ISOTYPE:</b>	IgG1,k
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	TARDBP, ALS10, TAR DNA-binding protein-43, TDP-43, TAR DNA binding protein, TAR DNA-binding protein 43, TDP43
<b>ACCESSION NO.:</b>	Q13148
<b>PROTEIN GI NO.:</b>	20140568
<b>OFFICIAL SYMBOL:</b>	TARDBP
<b>GENE ID:</b>	23435

