




Calnexin Antibody [1D4]

CATALOG NUMBER: 51-891



Immunohistochemistry of human placenta tissue stained using Calnexin Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	Calnexin antibody can be used in immunohistochemistry starting at 10 ug/mL, and flow cytometry starting at 1.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	CANX (NP_001737, 504 a.a. ~ 593 a.a) partial recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	Aliquot and store Calnexin antibody at -20 °C or -80 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2b,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CANX, CNX, Calnexin, IP90, p90
ACCESSION NO.:	P27824
PROTEIN GI NO.:	543920
OFFICIAL SYMBOL:	CANX
GENE ID:	821

Background

