



FN1 Antibody [16E5]

CATALOG NUMBER: 70-084

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	IHC, IP, WB
APPLICATIONS:	FN1 Monoclonal Antibody can be used for immunohistochemistry (tested on parafin embedded tissues) starting at 1:200 and Western Blot starting at 1:2000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Protein purified from Human plasma.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Ammonium Sulfate Precipitation
PHYSICAL STATE:	Liquid
BUFFER:	HEPES with 0.15M NaCl, 0.01% BSA, 0.03% sodium azide, and 50% glycerol
STORAGE CONDITIONS:	FN1 Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles. Store undiluted.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	FN1, CIG, Cold-insoluble globulin, Fibronectin 1, FINC, LETS, GFND, ED-B, Fibronectin, FN, FNZ, GFND2, Migration-stimulating factor, MSF
ACCESSION NO.:	P02751
PROTEIN GI NO.:	300669710
OFFICIAL SYMBOL:	FN1
GENE ID:	2335

Background

FOR RESEARCH USE ONLY

December 13, 2016