

# Matrix Scientific

PO BOX 25067

COLUMBIA, SC 29224-5067

Telephone: 803-788-9494

Fax: 803-788-9419

---

## SAFETY DATA SHEET

Transportation Emergency: 3E Co. (5025) 800-451-8346

### 1. Product Identification

---

**Name** 2-Ethoxyphenethylamine  
**Catalog Number** 003856  
**CAS Registry Number** [39590-27-7]  
**Company** Matrix Scientific  
**Physical Address** 131 Pontiac Business Center Drive  
Elgin, SC 29045  
USA  
**Telephone/Fax** (803)788-9494/(803)788-9419

### 2. Hazard Identification

---

**Hazardous Ingredients** 2-Ethoxyphenethylamine

**GHS label elements, including precautionary statements**

**Pictogram**



**Signal word** DANGER

**Hazard statement(s)**

H302	Harmful if swallowed
H314	Causes severe skin burns and eye damage
H317	May cause an allergic skin reaction
H318	Causes serious eye damage
H319	Causes serious eye irritation

**Precautionary statement(s)**

P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P260	Do not breathe dust/fume/gas/mist/vapours/spray.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P301+330+331	IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.
P303+361+353	IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/ shower.
P305+351+338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses if present and easy to do - continue rinsing.
P501	Dispose of contents/container to ... [... in accordance with

local/regional/national/international regulation (to be specified)].

### 3. **Composition, Information or Ingredients**

#### **Corrosive Irritant**

Avoid prolonged exposure.

Do Not breathe vapor.

Use caution when handling.

Exposure to any chemical should be limited.

To the best of our knowledge, the health hazards of this product have not been fully investigated.

This product is provided solely for the purpose of research and development.

### 4. **First Aid Measures**

<b>Eye Contact:</b>	Check for and remove any contact lenses. Immediately flush eyes with clean, running water for at least 15 minutes while keeping eyes open. Cool water may be used. Seek medical attention.
<b>Skin Contact:</b>	After contact with skin, wash with generous quantities of running water. Gently and thoroughly wash affected area with running water and non-abrasive soap. Cool water may be used. Cover the affected area with emollient. Seek medical attention. Wash any contaminated clothing prior to reusing.
<b>Inhalation:</b>	Remove the victim from the source of exposure to fresh, uncontaminated air. If victim's breathing is difficult, administer oxygen. Seek medical attention.
<b>Ingestion:</b>	Do NOT induce vomiting. Give water to victim to drink. Seek medical attention.

### 5. **Fire-Fighting Measures**

<b>Extinguishing media:</b>	Carbon dioxide, dry chemical powder, alcohol or polymer foam.
<b>Special fire fighting procedures:</b>	Wear self-contained breathing apparatus and protective clothing to prevent contact with skin and eyes.
<b>Unusual fire and explosion hazards/decomposition of product:</b>	Emits toxic fumes under fire conditions.

### 6. **Accidental Release Measures**

Steps to be taken if material is spilled or otherwise released into the environment - Wear Appropriate respirator, impervious boots and heavy rubber (or otherwise impervious) gloves. Scoop up solid material or absorb liquid material and place into appropriate container. Ventilate area and wash affected spill area after pickup is complete. Wash skin immediately with plenty of water. Place solid or absorbed material into containers and close for disposal.

## 7. Handling and Storage

---

Do not breath dust or vapor.  
Have safety shower and eye wash available.  
Do not get in eyes, on skin or on clothing.  
Keep container tightly closed.  
Store in a cool, dry, well-ventilated place.  
Ensure adequate ventilation during use.  
Use only in a chemical fume hood.

## 8. Exposure Controls and Personal Protection

---

Wear Protective safety goggles.  
Wear chemical-resistant gloves.  
Wear protective clothing and chemical resistant boots.  
Ensure ventilation during use.  
After contact with skin, wash immediately.

## 9. Physical and Chemical Properties

---

**Appearance:** liquid  
**Molecular Formula:** C<sub>10</sub>H<sub>15</sub>NO  
**Molecular Weight:** 165.24  
**Boiling point (C):** 118°/20mm  
**Density (g/ml):** 1.01

## 10. Stability and Reactivity

---

**Incompatibilities:** Strong oxidizing agents  
Strong acids and bases

**Hazard Decomposition Products**

**Carbon** carbon monoxide  
carbon dioxide

**Nitrogen** oxides of nitrogen

## 11. Toxicological Information

---

**Acute effects:**

Irritant

May be harmful by ingestion and inhalation.

Material is irritating to mucous membranes and upper respiratory tract.

To the best of our knowledge, the toxicological properties of this product have not been fully investigated or determined.

## 12. Ecological Information

---

<b>Mobility:</b>	Data not known
<b>Persistence and degradability:</b>	No data available
<b>Cumulative potential:</b>	No data available
<b>Other adverse effects:</b>	No data available

### 13. **Disposal Considerations**

---

Absent other actions demanded by federal or local regulations - Dissolve or mix the material with a combustible solvent and burn in a regulated, chemical incinerator equipped with after burner and scrubber.

Observe all federal, state and local laws.

### 14. **Transport Information**

---

**Shipping Name** Amines, liquid, corrosive, n.o.s.  
**Class / Sub-Class** 8  
**UN Number** UN2735  
**Packing Group** III  
**Inhalation Hazard Zone**

### 15. **Regulatory Information**

---

Adhere to all Federal, State and local regulations.

### 16. **Other Information**

---

The information contained herein is accurate to the best of our knowledge, but is not meant to be complete and is included only as a guide. The end user is responsible for any damage resulting from handling or from contact with this product.