



ATP6V1B2 Antibody [2A5]

CATALOG NUMBER: 70-175

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	ATP6V1B2 Monoclonal Antibody can be used for immunohistochemistry (tested on paraffin embedded tissues) starting at 5 ug/mL and Western Blot starting at 1:500 - 1:1000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant protein
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	ATP6V1B2 Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	ATP6V1B2, ATP6B1B2, ATP6B2, V-ATPase subunit B 2, Vma2, VATB, VPP3, HO57, V-ATPase B2 subunit
ACCESSION NO.:	P21281
PROTEIN GI NO.:	12643271
OFFICIAL SYMBOL:	ATP6V1B2
GENE ID:	526

Background

FOR RESEARCH USE ONLY

December 13, 2016